# FEXL9L942

#### **Base Product**



OM4 LC/UPC Keyed Rose to LC/UPC Keyed Rose Fiber Patch Cord, 1.6 mm Duplex, Riser

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Europe | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

**Product Type** Fiber patch cord, duplex

Product Brand SYSTIMAX InstaPATCH® 360

**Product Series** FEX

Ordering Note For lengths greater than 999 ft (304 m), orders must be in meters | Minimum length

may vary based on cable configuration

### General Specifications

Color, boot A Aqua

Color, connector A Rose

Color, boot B Aqua

Color, connector B Rose

Interface, Connector A LC/UPC

Interface Feature, connector A Keyed

Interface, Connector B LC/UPC

Interface Feature, connector B Keyed

Jacket Color Aqua

**Polarity** Method B

Total Fibers, quantity 2

#### **Dimensions**

Cable Assembly Length Range (m) 1 - 999


Cable Assembly Length Range (ft) 1 - 999

**Diameter Over Jacket** 1.6 mm | 0.063 in

COMMSC PE®

# FEXL9L942

## Ordering Tree



### Mechanical Specifications

Cable Retention Strength, maximum  $11.24 \text{ lb} @ 0 \degree | 4.40 \text{ lb} @ 90 \degree$ 

Optical Specifications

**Fiber Mode** Multimode

**Fiber Type** OM4, LazrSPEED®

## **Environmental Specifications**

**Operating Temperature**  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  ( $+14 \,^{\circ}\text{F}$  to  $+140 \,^{\circ}\text{F}$ )

Environmental Space Riser

## Regulatory Compliance/Certifications

Classification

Agency	Classification
ANATEL	Compliant
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Agency



#### Included Products

760102483 – LazrSPEED®, OptiSPEED® Pre-Radiused Keyed LC Connector for 1.6 mm Fiber, duplex multimode, rose

Page 2 of 8

# FEXL9L942

R-002-ZC-5K-F16

Fiber indoor cable, LazrSPEED® 1.6 mm Riser Zipcord, Multimode OM4, Feet jacket marking

**COMMSCOPE®** 

# 760102483 | MDC-LCR-16-KRO



LazrSPEED®, OptiSPEED® Pre-Radiused Keyed LC Connector for 1.6 mm Fiber, duplex multimode, rose

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type Fiber connector

General Specifications

Body Style Duplex
Color Rose

Ferrule Geometry Pre-radiused

InterfaceLC/UPCInterface FeatureKeyed

**Dimensions** 

 Length
 52 mm | 2.047 in

 Compatible Cable Diameter
 1.6 mm | 0.063 in

Material Specifications

Ferrule Material Zirconia

Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 °

Optical Specifications

Fiber Mode Multimode
Insertion Loss Change, mating 0.3 dB

Optical Components Standard ANSI/TIA-568-C.3

**COMMSCOPE®** 

# 760102483 | MDC-LCR-16-KRO

Insertion Loss Change, temperature0.3 dBInsertion Loss, typical0.2 dBReturn Loss, minimum50 dB

#### Packaging and Weights

Packaging quantity 2

## Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### \* Footnotes

**Insertion Loss Change, mating** TIA-568: Maximum insertion loss change after 500 matings

**Insertion Loss Change, temperature** Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)



# R-002-ZC-5K-F16

Fiber indoor cable, LazrSPEED® 1.6 mm Riser Zipcord, Multimode OM4, Feet jacket marking

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East/Africa | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber indoor cable

Product Series R-ZC

#### General Specifications


Cable TypeCordageConstruction TypeNon-armoredSubunit TypeGel-free

Jacket Marking Feet
Total Fiber Count 2

**Dimensions** 

Height Over Jacket1.7 mm0.067 inWidth Over Jacket3.5 mm0.138 in

### Representative Image



## Mechanical Specifications

Minimum Bend Radius, loaded 38 mm | 1.496 in

Page 6 of 8



# R-002-ZC-5K-F16

Minimum Bend Radius, unloaded15 mm0.591 inTensile Load, long term, maximum53 N11.915 lbf

Tensile Load, short term, maximum 178 N | 40.016 lbf

**Compression** 10 N/mm | 57.101 lb/in

**Compression Test Method** FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 500 m | 1,640.42 ft

Optical Specifications

Fiber Type OM4, LazrSPEED® 550 | OM4, LazrSPEED® 550

#### **Environmental Specifications**

Installation temperature  $-20 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-4 °F to  $+158 \,^{\circ}\text{F}$ )

Operating Temperature  $-20 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-4 °F to  $+158 \,^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40 °F to  $+158 \,^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Riser

Flame Test Listing NEC OFNR (ETL) and c(ETL)

Flame Test Method UL 1666

## **Environmental Test Specifications**

**Heat Age** -20 °C to +85 °C (-4 °F to +185 °F)

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend**  $-20~^{\circ}\text{C to } +70~^{\circ}\text{C } (-4~^{\circ}\text{F to } +158~^{\circ}\text{F})$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle** -20 °C to +70 °C (-4 °F to +158 °F)



# R-002-ZC-5K-F16

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 5.8 kg/km | 3.897 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

\* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

