

760074047



In-Line MPO Adapter Housing

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber adapter enclosure |
| Ordering Note | Minimum length may vary based on cable configuration |

General Specifications

| | |
|--------------------|---|
| Application | Additional protection when mating an InstaPATCH® Plus trunk cable to an InstaPATCH® Plus extension cable or ruggedized fanout |
| Interface | MPO |

Dimensions

| | |
|----------------------------------|-----------------|
| Compatible Cable Diameter | 3 mm 0.118 in |
|----------------------------------|-----------------|

Mechanical Specifications

| | |
|------------------------------|------------------|
| Tensile Load, maximum | 48.93 N 11 lbf |
|------------------------------|------------------|

Packaging and Weights

| | |
|-----------------|---|
| Included | Hook and loop fastener Housing Label Two MPO adapters |
|-----------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |



760074047
