

16-ports sector antenna, 2x 694-862 (R1), 2x 880-960 (R2), 2x 694-960 (R3), 2x 1427-2690 (Y3), 8x 1695-2690 (Y1,Y2,Y4,Y5) MHz ,65° HPBW, 8x RET

- Retractable tilt indicator rods
- 8 Internal RET's provide independent electrical tilt control for each array
- All Internal RET actuators are connected in "Cascaded SRET" configuration
- Supports re-configurable antenna sharing capability enabling control of the internal RET system using up to two separate RET compatible OEM radios
- Antenna shape optimized for wind load reduction

General Specifications

Antenna Type Sector with internal RET

Band Multiband

Color Light Gray (RAL 7035)

Grounding TypeRF connector inner conductor and body grounded to reflector and mounting

bracket

Performance Note Outdoor usage

Radome Material Fiberglass, UV resistant

Reflector Material Aluminum

RF Connector Interface 4.3-10 Female

RF Connector Location Bottom

RF Connector Quantity, high band 10
RF Connector Quantity, mid band 0

RF Connector Quantity, low band 6

RF Connector Quantity, total 16

Remote Electrical Tilt (RET) Information

RET Hardware CommRET v2

RET Interface 8-pin DIN Female | 8-pin DIN Male

RET Interface, quantity 2 female | 2 male

Input Voltage 10-30 Vdc

Internal RET High band (5) | Low band (3)

Power Consumption, active state, maximum 8 W

ANDREW® an Amphenol company

Page 1 of 6

Power Consumption, idle state, maximum 1 W

Protocol 3GPP/AISG 2.0 (Single RET)

Dimensions


 Width
 430 mm | 16.929 in

 Depth
 197 mm | 7.756 in

 Length
 2769 mm | 109.016 in

Net Weight, antenna only 55.8 kg | 123.018 lb


Array Layout



| Array ID | Frequency (MHz) | RF Connector | RET (SRET) | AISG RET UID | | |
|----------|-----------------|--------------|---------------|--------------------|--|--|
| R1 | 694-862 | 1 - 2 | 1 | CPxxxxxxxxxxxxxR1 | | |
| R2 | 880-960 | 3 - 4 | 2 | CPxxxxxxxxxxxxxxR2 | | |
| R3 | 694-960 | 5 - 6 | 3 | CPxxxxxxxxxxxxxR3 | | |
| Y1 | 1695-2690 | 7 - 8 | 4 | CPxxxxxxxxxxxxxY1 | | |
| Y2 | 1695-2690 | 9 - 10 | 5 | CPxxxxxxxxxxxxxY2 | | |
| Y3 | 1427-2690 | 11 - 12 6 | | CPxxxxxxxxxxxxxY3 | | |
| Y4 | 1695-2690 | 13 - 14 | 7 | CPxxxxxxxxxxxxY4 | | |
| Y5 | 1695-2690 | 15 - 16 | 8 | CPxxxxxxxxxxxxxY5 | | |

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration



Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 1427 – 2690 MHz | 1695 – 2690 MHz | 694 – 862 MHz | 694 – 960

MHz | 880 - 960 MHz

Polarization ±45°

Total Input Power, maximum 900 W @ 50 °C

Electrical Specifications

| | R1 | R2 | R3 | Y3 | Y3 | Y3 | Y1,Y2,Y4,Y | 5Y1,Y2,Y4,Y5 |
|--|------------|------------|------------|------------|------------|------------|------------|--------------|
| Frequency Band, MHz | 694-862 | 880-960 | 694-960 | 1427-1518 | 8 1695–218 | 2300-2690 | 1695-2200 | 2300-2690 |
| RF Port | 1,2 | 3,4 | 5,6 | 11,12 | 11,12 | 11,12 | 7-10,13-16 | 7-10,13-16 |
| Gain, dBi | 15.5 | 16.1 | 16.4 | 16.3 | 17.6 | 18.1 | 17.4 | 18.1 |
| Beamwidth, Horizontal, degrees | 59 | 54 | 58 | 58 | 56 | 62 | 59 | 58 |
| Beamwidth, Vertical, degrees | 7.3 | 6.3 | 6.9 | 7.2 | 5.6 | 4.4 | 6.2 | 5 |
| Beam Tilt, degrees | 2-12 | 2-12 | 2-12 | 2-12 | 2-12 | 2-12 | 2-12 | 2-12 |
| USLS (First Lobe), dB | 17 | 18 | 15 | 20 | 20 | 20 | 15 | 16 |
| Front-to-Back Ratio at 180°, dB | 34 | 31 | 31 | 35 | 31 | 32 | 32 | 32 |
| Isolation, Cross Polarization, dB | 27 | 27 | 27 | 26 | 26 | 26 | 27 | 27 |
| Isolation, Inter-band, dB | 27 | 27 | 27 | 27 | 27 | 27 | 27 | 27 |
| VSWR Return loss, dB | 1.5 14.0 | 1.5 14.0 | 1.5 14.0 | 1.5 14.0 | 1.5 14.0 | 1.5 14.0 | 1.5 14.0 | 1.5 14.0 |
| PIM, 3rd Order, 2 x 20 W, dBc | -153 | -153 | -153 | -153 | -153 | -153 | -153 | -153 |
| Input Power per Port at 50°C, maximum, watts | 300 | 300 | 300 | 250 | 250 | 200 | 250 | 200 |

Mechanical Specifications

 Wind Loading @ Velocity, frontal
 680.0 N @ 150 km/h (152.9 lbf @ 150 km/h)

 Wind Loading @ Velocity, lateral
 347.0 N @ 150 km/h (78.0 lbf @ 150 km/h)

 Wind Loading @ Velocity, maximum
 1,020.0 N @ 150 km/h (229.3 lbf @ 150 km/h)

 Wind Loading @ Velocity, rear
 434.0 N @ 150 km/h (97.6 lbf @ 150 km/h)

Wind Speed, maximum 241 km/h (150 mph)

Packaging and Weights

Width, packed 530 mm | 20.866 in

ANDREW® an Amphenol company

 Depth, packed
 356 mm | 14.016 in

 Length, packed
 2897 mm | 114.055 in

 Weight, gross
 76.8 kg | 169.315 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

BSAMNT-4 – Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members.

Kit contains one scissor top bracket set and one bottom bracket set.

BSAMNT-M4 – Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round

members. Kit contains one scissor bracket set.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance



BSAMNT-4



Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

Product Classification

Product Type Downtilt mounting kit

General Specifications

ApplicationOutdoorColorSilver

Dimensions

Compatible Diameter, maximum115 mm | 4.528 inCompatible Diameter, minimum60 mm | 2.362 inWeight, net6.5 kg | 14.33 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Below maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| REACH-SVHC | Compliant as per SVHC revision on www.andrew.com/ProductCompliance |
| ROHS | Compliant |
| UK-ROHS | Compliant |
| | |



BSAMNT-M4



Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor bracket set.

Product Classification

Product Type Downtilt mounting kit

General Specifications

ApplicationOutdoorColorSilver

Dimensions

Compatible Diameter, maximum115 mm | 4.528 inCompatible Diameter, minimum60 mm | 2.362 inWeight, net4.6 kg | 10.141 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



