

# APTDC-BDFDF-DB



Arrestor Plus® LTE Band Quarterwave dc Passing Surge Arrestor (T-shaped), 698–2170 MHz, with interface types DIN Female Bulkhead and DIN Female

OBSOLETE

## Product Classification

Product Type	Quarter wave shorting stub
Product Brand	Arrestor Plus®
Ordering Note	ANDREW® standard product in the United States and Canada

## General Specifications


Device Type	dc Pass
Body Style	Bulkhead
Inner Contact Plating	Silver
Interface	7-16 DIN Female Bulkhead
Interface 2	7-16 DIN Female
Outer Contact Plating	Trimetal
Pressurizable	No

## Dimensions

Height	81 mm   3.189 in
Width	42 mm   1.654 in
Length	88 mm   3.465 in

## Outline Drawing

# APTDC-BDFDF-DB



## Electrical Specifications

3rd Order IMD	-117 dBm
3rd Order IMD Test Method	Two +43 dBm carriers
Insertion Loss, typical	0.05 dB
Average Power	3000 W
Connector Impedance	50 ohm
Gas Tube Voltage	350 V
Lightning Surge Capability	10 times @ 30 kA
Lightning Surge Capability Test Method	IEEE C62.42-1991
Lightning Surge Capability Waveform	8/20 waveform
Lightning Surge Current	30 kA
Lightning Surge Current Waveform	8/20 waveform
Operating Frequency Band	698 – 2170 MHz
Peak Power, maximum	40 kW

## VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
1.0–5.0 MHz	1.173	22
2.0–2.3 MHz	1.119	25
698–806 MHz	1.208	20.5
806–960 MHz	1.135	24
1710–2000 MHz	1.106	26

# APTDC-BDFDF-DB

2000–2170 MHz	1.106	26
---------------	-------	----

## Mechanical Specifications

Attachment Durability	25 cycles
Interface Durability	500 cycles
Interface Durability Method	IEC 61169-16:9.5
Mechanical Shock Test Method	MIL-STD-202F, Method 213B, Test Condition C

## Environmental Specifications

Operating Temperature	-40 °C to +100 °C (-40 °F to +212 °F)
Storage Temperature	-70 °C to +150 °C (-94 °F to +302 °F)
Attenuation, Ambient Temperature	20 °C   68 °F
Average Power, Ambient Temperature	40 °C   104 °F
Corrosion Test Method	MIL-STD-202, Method 101, Test Condition B
Immersion Depth	1 m
Immersion Test Mating	Mated
Immersion Test Method	IEC 60529:2001, IP68
Moisture Resistance Test Method	MIL-STD-202, Method 106
Thermal Shock Test Method	MIL-STD-202, Method 107, Test Condition A-1, Low Temperature -55 °C
Water Jetting Test Mating	Mated

## Packaging and Weights

Weight, net	0.64 kg   1.41 lb
-------------	-------------------

## Regulatory Compliance/Certifications

Agency	Classification
AISG	Compliant
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

