

F4S-DMDR-3M-P

RSJ4-50 SureFlex® Jumper with interface types 7/16 DIN Male and 7-16 DIN Right Angle Male, 3m



Product Classification

| | |
|-----------------------|-------------------------------|
| Product Type | SureFlex® Premium, static PIM |
| Product Series | RSJ4-50 |

General Specifications

| | |
|---|---------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Right angle |
| Interface, Connector A | 7-16 DIN Male |
| Interface, Connector B | 7-16 DIN Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|----------------|
| Length | 3 m 9.843 ft |
| Nominal Size | 1/2 in |

Electrical Specifications

| | |
|---|----------------------|
| 3rd Order IMD Static | -116 dBm |
| 3rd Order IMD Static Test Method | Two +43 dBm carriers |
| DTF, Connector A | 34 dB |
| DTF, Connector B | 32 dB |

VSWR/Return Loss

| Frequency Band | VSWR | Return Loss (dB) |
|----------------|-------|------------------|
| 698–960 MHz | 1.083 | 27.99 |
| 1700–2200 MHz | 1.083 | 27.99 |
| 2200–2700 MHz | 1.135 | 23.98 |

F4S-DMDR-3M-P

3400-3800 MHz

1.222

20.01

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system



Included Products

RSJ4-50

- RSJ4-50, HELIAX[®] Superflexible Foam Coaxial Cable, corrugated copper, 1/2 in, black PE jacket