

F4A-HPDFDR-2M5

HELIAX® 1/2" SureFlex® Jumper with interface types 7-16 DIN Female and 7-16 DIN Male Right Angle, 2.5 m



Product Classification

| | |
|-----------------------|-----------------------------------|
| Product Type | SureFlex® HP, HELIAX® performance |
| Product Series | RSJ4-50 |

General Specifications

| | |
|---|-----------------|
| Body Style, Connector A | Straight |
| Body Style, Connector B | Right angle |
| Interface, Connector A | 7-16 DIN Female |
| Interface, Connector B | 7-16 DIN Male |
| Specification Sheet Revision Level | A |

Dimensions

| | |
|---------------------|------------------|
| Length | 2.5 m 8.202 ft |
| Nominal Size | 1/2 in |

Electrical Specifications

| | |
|---|----------------------|
| 3rd Order IMD Static Test Method | Two +43 dBm carriers |
| 3rd Order IMD, typical | -116 dBm |
| DTF, Connector A | -34 dB |
| DTF, Connector B | -32 dB |

VSWR/Return Loss

| Frequency Band | VSWR, typical | Return Loss, typical (dB) |
|----------------|---------------|---------------------------|
| 680–960 MHz | 1.083 | 27.99 |
| 1700–2200 MHz | 1.083 | 27.99 |
| 2200–2700 MHz | 1.135 | 23.98 |

F4A-HPDFDR-2M5

Jumper Assembly Sample Label



Environmental Specifications

Immersion Test Method

Meets IEC 60529:2001, IP68 in mated condition

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system

