

PFU-12-C-0-060-01



Power Extender, Universal Mount, Outdoor, 12 Vdc, Fiber Pass Through

- Environmentally sealed and tested
- Electrical power management
- Circuit protection electronics
- Automatically conditions electrical voltage to the correct level

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Power extender

General Specifications

Color Aluminum

Mounting Universal pole mount | Universal wall mount

Total Ports, quantity 1

Transition Performance 1 port, 60W at 12 Vdc

Transmission Standards CISPR 22/FCC CFR 47 | EN300386/FCC CFR 47 | ETSI EN 300 019-1-4 | IEC 60950-1 | IEC 60950-22 | NEC Class II

Transmission Standard Note NEC Class II requires a power supply unit (PSU) limited to less than 60V DC

Dimensions

Height 224.71 mm | 8.847 in

Width 283 mm | 11.142 in

Depth 77.02 mm | 3.032 in

Material Specifications

Finish White solar shield

Material Type Aluminum

Environmental Specifications

Installation temperature -5 °C to +45 °C (+23 °F to +113 °F)

Operating Temperature -40 °C to +65 °C (-40 °F to +149 °F)

PFU-12-C-0-060-01

Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Space	Outdoor
Qualification Standards	ETSI EN 300 019-1-4 IEC 60529, IP68 IEC 60950-22 IEC 62368
Safety Standard	CE CSA FCC RCM SELV WEEE

Packaging and Weights

Weight, net 5.08 kg | 11.199 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

