

DB201-P



1-port omni ground plane antenna, 450–470 MHz, 360° HPBW, fixed electrical tilt. Bandwidth: 2% of frequency.

- Omnidirectional antenna
- Mounts to top of tower, pole, or building
- Field tunable to desired frequency, cutting chart included

General Specifications

Antenna Type	Omni
Band	Single band
Color	Silver
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radiator Material	Aluminum
RF Connector Interface	N Male
RF Connector Location	Bottom
RF Connector Quantity, high band	0
RF Connector Quantity, mid band	0
RF Connector Quantity, low band	1
RF Connector Quantity, total	1

Dimensions

Width	226.1 mm 8.902 in
Depth	218.4 mm 8.598 in
Length	482.6 mm 19 in
Net Weight, without mounting kit	2.7 kg 5.952 lb

Electrical Specifications

Bandwidth	2% of frequency
Impedance	50 ohm
Operating Frequency Band	450 – 470 MHz
Polarization	Vertical

DB201-P

Electrical Specifications

Frequency Band, MHz	450–470
Gain, dBi	2.1
Beamwidth, Horizontal, degrees	360
Beamwidth, Vertical, degrees	78
Beam Tilt, degrees	0
VSWR Return loss, dB	1.5 14.0
Input Power per Port, maximum, watts	500

Mechanical Specifications

Wind Loading @ Velocity, maximum	53.4 N @ 100 mph (12.0 lbf @ 100 mph)
Wind Speed, maximum	201 km/h (125 mph)

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

DB365-OS	–	Pipe Mounting Kit that consists of two clamps for mounting antennas to round members 1.25 - 3.5 in (35 - 89 mm) OD round members.
----------	---	---

* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
------------------	---

DB365-0S

Pipe Mounting Kit that consists of two clamps for mounting antennas to round members 1.25 - 3.5 in (35 - 89 mm) OD round members.

Product Classification

Product Type Pipe mounting kit

General Specifications

Application Outdoor

Color Silver

Dimensions

Compatible Diameter, maximum 88.9 mm | 3.5 in

Compatible Diameter, minimum 33 mm | 1.299 in

Weight, net 3.2 kg | 7.055 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity 2

Weight, gross 3.6 kg | 7.937 lb

Regulatory Compliance/Certifications

Agency

CE

CHINA-ROHS

ISO 9001:2015

REACH-SVHC

ROHS

UK-ROHS

Classification

Compliant with the relevant CE product directives

Below maximum concentration value

Designed, manufactured and/or distributed under this quality management system

Compliant as per SVHC revision on www.andrew.com/ProductCompliance

Compliant

Compliant

