# DB404-B



1-port omni exposed dipole antenna, 450–470 MHz, 360° HPBW, fixed electrical tilt

### General Specifications

Antenna Type Omni

**Band** Single band

**Color** Silver

**Grounding Type** RF connector inner conductor and body grounded to reflector and mounting bracket

Performance Note Outdoor usage

Radiator Material Aluminum
RF Connector Interface N Male

**RF Connector Location** End of flexible lead

RF Connector Quantity, low band 1
RF Connector Quantity, total 1

Dimensions

**Length** 1524 mm | 60 in

Net Weight, without mounting kit 6.4 kg | 14.11 lb

Electrical Specifications

**Impedance** 50 ohm

**Operating Frequency Band** 450 – 470 MHz

**Polarization** Vertical

### **Electrical Specifications**

Frequency Band, MHz 450-470 Gain, dBi 5.9

Beamwidth, Horizontal, 360

degrees

Beamwidth, Vertical, degrees 27
Beam Tilt, degrees 0

**COMMSCOPE®** 

# DB404-B

VSWR | Return loss, dB

1.5 | 14.0

Input Power per Port, maximum, watts

250

### Mechanical Specifications

Wind Speed, maximum

161 km/h (100 mph)

## Regulatory Compliance/Certifications

#### Agency Classification

CE Compliant with the relevant CE product directives

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



#### Included Products

DB365-OS

Pipe Mounting Kit that consists of two clamps for mounting antennas to round members 1.25 3.5 in (35 - 89 mm) OD round members.

### \* Footnotes

**Performance Note** 

Severe environmental conditions may degrade optimum performance

