## FE-12104-G-R4



HELIAX® Fiber and Power Junction Box for 1 Hybrid Trunk / 4 Hybrid Jumper Cables with Internal Grounding

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America	
Product Type	Outdoor junction box	
Product Brand	HELIAX®	
General Specifications		
Application	Used as a fiber/power junction box	
Cable Entry, quantity, maximum, bottom	5	
Color	Gray	
Fiber System Configuration Type	Hybrid with junction box, 4 RRU	
Mounting	Pipe, 44–114 mm (1.75–4.5 in) OD   Wall	
Dimensions		
Height	317.5 mm   12.5 in	
Width	266.7 mm   10.5 in	
Depth	101.6 mm   4 in	
Cable Entry Fiber Gland Size, maximum	25 mm   0.984 in	
Cable Entry Fiber Gland Size, minimum	18 mm   0.709 in	
Cable Entry Jumper Gland Size, maximum	18 mm   0.709 in	
Cable Entry Jumper Gland Size, minimum	13 mm   0.512 in	
Compatible Center Conductor Gauge	10 AWG   12 AWG	
Material Specifications		

Material Type

High-impact polycarbonate, UV resistant

## **Environmental Specifications**

**Operating Temperature** 

-40 °C to +75 °C (-40 °F to +167 °F)



©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025

## FE-12104-G-R4

Environmental Space		Indoor   Outdoor
Qualification Standards		IEC 60529:2001, IP67
Packaging and Weights		
Included		Mounting kit
Weight, net		1.579 kg   3.48 lb
Regulatory Compliance/Certifications		
Agency	Classification	
CHINA-ROHS	Below maximum concentration value	
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system	
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance	
ROHS	Compliant	
UK-ROHS	Compliant	







©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025