

DB633-C



1-port omni antenna, 450–482 MHz, 360° HPBW, fixed electrical tilt

- Omnidirectional antenna
- Rugged, durable design, heavy duty radome for minimum tip deflection
- Invert mountable

General Specifications

Antenna Type	Omni
Band	Single band
Color	Horizon blue
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Radiator Material	Brass
RF Connector Interface	N Female
RF Connector Location	Bottom
RF Connector Quantity, high band	0
RF Connector Quantity, mid band	0
RF Connector Quantity, low band	1
RF Connector Quantity, total	1

Dimensions

Length	1435 mm 56.496 in
Net Weight, without mounting kit	3.6 kg 7.937 lb
Outer Diameter	50.8 mm 2 in

Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	450 – 482 MHz
Polarization	Vertical

Electrical Specifications

Frequency Band, MHz	450–482
----------------------------	----------------

DB633-C

Gain, dBi	5.1
Beamwidth, Horizontal, degrees	360
Beamwidth, Vertical, degrees	35
Beam Tilt, degrees	0
VSWR Return loss, dB	1.5 14.0
Input Power per Port, maximum, watts	500

Mechanical Specifications

Wind Loading @ Velocity, maximum	87.2 N @ 100 mph (19.6 lbf @ 100 mph)
Wind Speed, maximum	201 km/h (125 mph)

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

DB365-OS	-	Pipe Mounting Kit that consists of two clamps for mounting antennas to round members 1.25 - 3.5 in (35 - 89 mm) OD round members.
----------	---	---

* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
-------------------------	---