LDXX-6515DS-VTM | LDXX-6515DS-A2M



4-port sector antenna, 4x 790-960 MHz, 65° HPBW, RET compatible

- Two DualPol® antennas under one radome
- Each DualPol® array can be independently adjusted for greater flexibility
- Engineered to provide wideband capability to support "Digital Dividend" band applications, future ready

OBSOLETE

This product was discontinued on: March 31, 2023

Replaced By:

4P-4L-B2 4-port sector antenna, 4x 694-960 MHz, 65° HPBW

General Specifications

Antenna Type Sector

Band Single band

Color Light Gray (RAL 7035)

Grounding TypeRF connector inner conductor and body grounded to reflector and

mounting bracket

Performance Note Outdoor usage

Radome Material Fiberglass, UV resistant

Radiator MaterialAluminumReflector MaterialAluminum

RF Connector Interface 7-16 DIN Female

RF Connector Location Bottom

RF Connector Quantity, high band 0

RF Connector Quantity, mid band 0

RF Connector Quantity, low band 4

RF Connector Quantity, total 4

Remote Electrical Tilt (RET) Information

Model with Factory Installed AISG 2.0 Actuator LDXX-6515DS-A2M

Dimensions



LDXX-6515DS-VTM | LDXX-6515DS-A2M

 Width
 549 mm | 21.614 in

 Depth
 165 mm | 6.496 in

 Length
 2070 mm | 81.496 in

 Net Weight, without mounting kit
 35.6 kg | 78.484 lb

Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 790 – 960 MHz

Polarization ±45°

Electrical Specifications

| Frequency Band, MHz | 790-862 | 824-894 | 870-960 |
|--|------------|------------|------------|
| Gain, dBi | 16.3 | 16.4 | 17 |
| Beamwidth, Horizontal, degrees | 68.1 | 65.9 | 63 |
| Beamwidth, Vertical, degrees | 10.4 | 10 | 9.6 |
| Beam Tilt, degrees | 0-10 | 0-10 | 0-10 |
| USLS (First Lobe), dB | 18 | 18 | 17 |
| Front-to-Back Ratio at 180°, dB | 32 | 28 | 27 |
| Front-to-Back Total Power at 180° ± 30°, dB | 26 | 25 | 23 |
| CPR at Boresight, dB | 24 | 23 | 23 |
| CPR at Sector, dB | 14 | 13 | 10 |
| Isolation, Cross Polarization, dB | 30 | 30 | 30 |
| VSWR Return loss, dB | 1.4 15.6 | 1.4 15.6 | 1.4 15.6 |
| PIM, 3rd Order, 2 x 20 W, dBc | -150 | -150 | -150 |
| Input Power per Port, maximum, watts | 350 | 350 | 350 |

Mechanical Specifications

 Wind Loading @ Velocity, frontal
 1,407.0 N @ 150 km/h (316.3 lbf @ 150 km/h)

 Wind Loading @ Velocity, lateral
 337.0 N @ 150 km/h (75.8 lbf @ 150 km/h)

 Wind Loading @ Velocity, rear
 1,558.0 N @ 150 km/h (350.3 lbf @ 150 km/h)

Wind Speed, maximum 241 km/h (150 mph)

Packaging and Weights

Width, packed 693 mm | 27.283 in



_DXX-6515DS-VTM | LDXX-6515DS-A2M

 Depth, packed
 291 mm | 11.457 in

 Length, packed
 2294 mm | 90.315 in

 Weight, gross
 54.8 kg | 120.813 lb

Regulatory Compliance/Certifications

| Agency | Classification |
|--------|----------------|
|--------|----------------|

CE Compliant with the relevant CE product directives

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

BSAMNT-3 – Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members.

Kit contains one scissor top bracket set and one bottom bracket set.

BSAMNT-M – Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round

members. Kit contains one scissor bracket set.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance



BSAMNT-3



Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

Product Classification

Product Type Downtilt mounting kit

General Specifications

ApplicationOutdoorColorSilver

Dimensions

Agency

UK-ROHS

Compatible Diameter, maximum115 mm | 4.528 inCompatible Diameter, minimum60 mm | 2.362 inWeight, net6.2 kg | 13.669 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity

Weight, gross 6.4 kg | 14.11 lb

Regulatory Compliance/Certifications

Classification

Compliant

CE Compliant with the relevant CE product directives CHINA-ROHS Below maximum concentration value ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance ROHS Compliant



Page 4 of 6



BSAMNT-M



Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor bracket set.

Product Classification

Product Type Downtilt mounting kit

General Specifications

ApplicationOutdoorColorSilver

Dimensions

Compatible Diameter, maximum115 mm | 4.528 inCompatible Diameter, minimum60 mm | 2.362 inWeight, net4.5 kg | 9.921 lb

Material Specifications

Material Type Galvanized steel

Packaging and Weights

Included Brackets | Hardware

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



ANDREW® an Amphenol company