

#### 10-port sector antenna, 4x 694–960 and 6x 1695–2690 MHz, 65° HPBW, 5x RET

- All Internal RET actuators are connected in "Cascaded SRET" configuration
- Supports re-configurable antenna sharing capability enabling control of the internal RET system using up to two separate RET compatible OEM radios

#### OBSOLETE

This product was discontinued on: February 28, 2025

#### **General Specifications**

BandMultibandGrounding TypeRF connector inner conductor and body grounded to reflector and mounting bracketPerformance NoteOutdoor usage   Wind loading figures are validated by wind tunnel measurements described in white paper WP-112534-ENRadome MaterialFiberglass, UV resistantRadiator MaterialLow loss circuit boardReflector MaterialAluminumRF Connector InterfaceBottomRF Connector LocationBottomRF Connector Quantity, high bandG	Antenna Type	Sector
Performance NoteOutdoor usage   Wind loading figures are validated by wind tunnel measurements described in white paper WP-112534-ENRadome MaterialFiberglass, UV resistantRadiator MaterialLow loss circuit boardReflector MaterialAluminumRF Connector Interface4.3-10 FemaleRF Connector LocationBottomRF Connector Quantity, high band6	Band	Multiband
Radome MaterialFiberglass, UV resistantRadiator MaterialLow loss circuit boardReflector MaterialAluminumRF Connector Interface4.3-10 FemaleRF Connector LocationBottomRF Connector Quantity, high band6	Grounding Type	, ,
Radiator MaterialLow loss circuit boardReflector MaterialAluminumRF Connector Interface4.3-10 FemaleRF Connector LocationBottomRF Connector Quantity, high band6	Performance Note	
Reflector MaterialAluminumRF Connector Interface4.3-10 FemaleRF Connector LocationBottomRF Connector Quantity, high band6	Radome Material	Fiberglass, UV resistant
RF Connector Interface4.3-10 FemaleRF Connector LocationBottomRF Connector Quantity, high band6	Radiator Material	Low loss circuit board
<b>RF Connector Location</b> Bottom <b>RF Connector Quantity, high band</b> 6	Reflector Material	Aluminum
<b>RF Connector Quantity, high band</b> 6	RF Connector Interface	4.3-10 Female
	RF Connector Location	Bottom
	RF Connector Quantity, high band	6
<b>RF Connector Quantity, mid band</b> 0	RF Connector Quantity, mid band	0
RF Connector Quantity, low band 4	RF Connector Quantity, low band	4
RF Connector Quantity, total 10	RF Connector Quantity, total	10

### Remote Electrical Tilt (RET) Information

RET Hardware	CommRET v2
RET Interface	8-pin DIN Female   8-pin DIN Male
RET Interface, quantity	2 female   2 male
Input Voltage	10-30 Vdc
Internal RET	High band (3)   Low band (2)

Page 1 of 6



## RRV3-65D-R5

Power Consumption, idle state, maximum	1 W		
Power Consumption, normal conditions, maximum	8 W		
Protocol	3GPP/AISG 2.0 (Single RET)		
Dimensions			
Width	498 mm   19.606 in		
Depth	197 mm   7.756 in		
Length	2688 mm   105.827 in		
Net Weight, without mounting kit	43.2 kg   95.24 lb		

### Array Layout

Y2

**Y1** R1

		Array	Freq (MHz)	Conns	RET (SRET)	AISG RET UID
		R1	694-960	1-2	1	CPxxxxxxxxxxxxxR1
		R2	694-960	3-4	2	CPxxxxxxxxxxxxxR2
1		Y1	1695-2690	5-6	3	CPxxxxxxxxxxxxxXXXXXXXXY1
		Y2	1695-2690	7-8	4	CPxxxxxxxxxxxxXXXXXXY2
	Y3	Y3	1695-2690	9-10	5	CPxxxxxxxxxxxxXXXXXXXXXXXY3

Left Right Bottom

(Sizes of colored boxes are not true depictions of array sizes)

## **Electrical Specifications**

R2

Impedance	50 ohm
Operating Frequency Band	1695 – 2690 MHz   694 – 960 MHz
Polarization	±45°
Total Input Power, maximum	1,800 W @ 50 °C

### **Electrical Specifications**

Frequency Band, MHz	694-790	790-890	880-960	1695-188	0 1850–199	0 1920–218	0 2300-250	0 2500-2690
Gain, dBi	15.8	16.4	16.8	17	17.6	17.8	18.3	17.8
Beamwidth, Horizontal,	70	67	62	59	60	61	61	69

Page 2 of 6



# RRV3-65D-R5

· · <b>J</b>								
Beamwidth, Vertical, degrees	8.1	7.4	6.8	7.5	7	6.6	5.7	5.3
Beam Tilt, degrees	2-12	2-12	2-12	2-12	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	12	16	17	20	20	20	18	16
Front-to-Back Ratio at 180°, dB	32	32	33	37	38	36	34	33
Isolation, Cross Polarization, dB	28	28	28	28	28	28	28	28
Isolation, Inter-band, dB	30	30	30	30	30	30	30	30
VSWR   Return loss, dB	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150	-150	-150
Input Power per Port at 50°C, maximum, watts	350	350	350	300	300	300	250	250

### Mechanical Specifications

Mechanical Tilt Range	0°-12°
Wind Loading @ Velocity, frontal	1,070.0 N @ 150 km/h (240.5 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	375.0 N @ 150 km/h (84.3 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	1,385.0 N @ 150 km/h (311.4 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	880.0 N @ 150 km/h (197.8 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

### Packaging and Weights

Width, packed	565 mm   22.244 in
Depth, packed	309 mm   12.165 in
Length, packed	2935 mm   115.551 in
Weight, gross	64.1 kg   141.316 lb

## Regulatory Compliance/Certifications

CHINA-ROHS Above maximum concentration value
ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system
ROHS Compliant/Exempted
UK-ROHS Compliant/Exempted



Page 3 of 6



### Included Products

BSAMNT-4	<ul> <li>Wide Profile Antenna Downtilt Mountil</li> <li>Kit contains one scissor top bracket s</li> </ul>	ng Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. et and one bottom bracket set.
BSAMNT-M4	<ul> <li>Middle Downtilt Mounting Kit for Long members. Kit contains one scissor bra</li> </ul>	) Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round acket set.
* Footnotes		

Performance Note Severe environmental conditions may degrade optimum performance



Page 4 of 6

s. ANDREW an Amphenol company

## BSAMNT-4



Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

Product Classification	
Product Type	Downtilt mounting kit
General Specifications	
Application	Outdoor
Color	Silver
Dimensions	
Compatible Diameter, maximum	115 mm   4.528 in
Compatible Diameter, minimum	60 mm   2.362 in
Weight, net	6.5 kg   14.33 lb
Material Specifications	
Material Type	Galvanized steel
Packaging and Weights	
Included	Brackets   Hardware
Packaging quantity	1
Regulatory Compliance/Certifications	

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 5 of 6



# BSAMNT-M4



Middle Downtilt Mounting Kit for Long Antennas for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor bracket set.

Product Classification		
Product Type	Downtilt mounting kit	
General Specifications		
Application	Outdoor	
Color	Silver	
Dimensions		
Compatible Diameter, maximum	115 mm   4.528 in	
Compatible Diameter, minimum	60 mm   2.362 in	
Weight, net	4.6 kg   10.141 lb	
Material Specifications		
Material Type	Galvanized steel	
Packaging and Weights		
Included	Brackets   Hardware	
Packaging quantity	1	
Dogulatory Compliance /Cortifications		

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 6 of 6

