

2.4m | 8ft Sentinel® Ultra High Performance, Super High XPD Antenna, dual-polarized, 10.000 – 11.700 GHz, PDR100 flange

Product Classification

Product Type Microwave antenna

Product Brand Sentinel®

General Specifications

Antenna Type USX - Sentinel® Ultra High Performance, Super

High XPD Antenna, dual-polarized

Polarization Dual

Antenna Input PDR100

Antenna Color Gray

Reflector Construction One-piece reflector

Radome ColorGrayRadome MaterialFabricFlash IncludedYes

Side Struts, Included 1

Side Struts, Optional 4

Dimensions

Diameter, nominal 2.4 m | 8 ft

Electrical Specifications

Operating Frequency Band 10.000 - 11.700 GHz

Gain, Low Band45.4 dBiGain, Mid Band46 dBiGain, Top Band46.6 dBiBoresite Cross Polarization Discrimination (XPD)40 dB

Front-to-Back Ratio 80 dB

Beamwidth, Horizontal $\,$ 0.9 $^{\circ}$



Beamwidth, Vertical 0.9 °

Return Loss 26 dB

VSWR 1.1

Radiation Pattern Envelope Reference (RPE) 7398

Electrical Compliance ACMA FX03_10a | ACMA FX03_11a | ETSI 302

217 Class 4 | US FCC Part 105A | US FCC Part

107A

Cross Polarization Discrimination (XPD) Electrical Compliance ETSI EN 302217 XPD Category 3

Mechanical Specifications

Compatible Mounting Pipe Diameter 115 mm | 4.5 in

Fine Azimuth Adjustment Range ±5°

Fine Elevation Adjustment Range ±5°


 Wind Speed, operational
 180 km/h | 111.847 mph

 Wind Speed, survival
 200 km/h | 124.274 mph



Antenna Dimensions and Mounting Information

USX8



Dimensions in inches (mm)									
Antenna size, ft (m)	Α	В	С	D1	D2	Е	F	G	
8 (2.4)	95.1 (2416)	8.0 (203)	22.5 (572)	14.1 (357)	23.6 (600)	51.1 (1298)	12.1 (306)	10.3 (262)	

Wind Forces at Wind Velocity Survival Rating

Axial Force (FA) 10599 N | 2,382.751 lbf

Angle α for MT Max -140°

Side Force (FS) 6268 N | 1,409.103 lbf

Twisting Moment (MT) -7647 N-m | -67,681.656 in lb

Force on Inboard Strut Side 11263 N | 2,532.024 lbf

Zcg without Ice 624 mm | 24.567 in


Zcg with 1/2 in (12 mm) Radial Ice 765 mm | 30.118 in

Weight with 1/2 in (12 mm) Radial Ice 364 kg | 802.482 lb





Wind Forces at Wind Velocity Survival Rating Image



Packaging and Weights

Height, packed	2250 mm 88.583 in
Width, packed	1130 mm 44.488 in
Length, packed	2380 mm 93.701 in

Packaging Type Standard pack

 Volume
 6.1 m³ | 215.42 ft³

 Weight, gross
 329 kg | 725.32 lb

 Weight, net
 196 kg | 432.106 lb

Regulatory Compliance/Certifications



Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

* Footnotes

Operating Frequency Band

Bands correspond with CCIR recommendations or common

allocations used throughout the world. Other ranges can be

accommodated on special order.

Gain, Mid BandFor a given frequency band, gain is primarily a function of

antenna size. The gain of Andrew antennas is determined by either gain by comparison or by computer integration of the

measured antenna patterns.

Boresite Cross Polarization Discrimination (XPD)

The difference between the peak of the co-polarized main

beam and the maximum cross-polarized signal over an angle twice the 3 dB beamwidth of the co-polarized main beam.

Front-to-Back Ratio

Denotes highest radiation relative to the main beam, at 180°

±40°, across the band. Production antennas do not exceed rated values by more than 2 dB unless stated otherwise.

Return LossThe figure that indicates the proportion of radio waves

incident upon the antenna that are rejected as a ratio of

those that are accepted.

VSWR Maximum; is the guaranteed Peak Voltage-Standing-Wave-

Ratio within the operating band.

Radiation Pattern Envelope Reference (RPE)

Radiation patterns define an antenna's ability to discriminate

against unwanted signals. Under still dry conditions, production antennas will not have any peak exceeding the current RPE by more than 3dB, maintaining an angular

accuracy of +/-1° throughout

Cross Polarization Discrimination (XPD) Electrical Compliance The difference between the peak of the co-polarized main

beam and the maximum cross-polarized signal over an angle twice the 3 dB beamwidth of the co-polarized main beam.

Wind Speed, operational For VHLP(X), SHP(X), HX and USX antennas, the wind speed

where the maximum antenna deflection is $0.3\,\mathrm{x}$ the $3\,\mathrm{dB}$ beam width of the antenna. For other antennas, it is defined

as a deflection is equal to or less than 0.1 degrees.

Wind Speed, survival

The maximum wind speed the antenna, including mounts

and radomes, where applicable, will withstand without permanent deformation. Realignment may be required. This wind speed is applicable to antenna with the specified

amount of radial ice.

ANDREW®
an Amphenol company

Axial Force (FA)

Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Side Force (FS)

Maximum side force exerted on the mounting pipe as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Twisting Moment (MT)

Maximum forces exerted on a supporting structure as a result of wind from the most critical direction for this parameter. The individual maximums specified may not occur simultaneously. All forces are referenced to the mounting pipe.

Packaging Type

Andrew standard packing is suitable for export. Antennas are shipped as standard in totally recyclable cardboard or wirebound crates (dependent on product). For your convenience, Andrew offers heavy duty export packing options.