VVSSP-360S-D



10-port small cell antenna, 4x 1695–2690, 4x 3300-4200 and 2x 5150-5925 MHz. 360° Horizontal Beamwidth, fix tilt

- Nominal 4 inch diameter through-hole for mid pipe mount
- Accommodates central pipe up to 3.5" OD

General Specifications

Antenna Type Small Cell

Band Multiband

Grounding TypeRF connector inner conductor and body grounded to reflector and mounting

bracket

10

Performance Note Outdoor usage

Radome Material ASA

Radiator Material Aluminum | Low loss circuit board

Reflector Material Aluminum

RF Connector Interface 4.3-10 Female

RF Connector Location

RF Connector Quantity, high band

RF Connector Quantity, mid band

0

RF Connector Quantity, low band

0

Dimensions

RF Connector Quantity, total

 Length
 618 mm | 24.331 in

 Net Weight, without mounting kit
 10.6 kg | 23.369 lb

 Outer Diameter
 305 mm | 12.008 in

5 GHz Port Power Table



VVSSP-360S-D

5 GHz FCC Power Requirements				
U-NII Band	U-NII 1	U-NII 2A	U-NII 2C	U-NII 3
Frequency (MHz)	5150 - 5250	5250 - 5350	5470 - 5725	5725 - 5850
Max Input power per port to align with FCC Title 47 Part 15 (Watts)	0.5	0.125	0.125	0.5

Port Configuration



Electrical Specifications

Impedance 50 ohm

Operating Frequency Band 1695 – 2690 MHz | 3300 – 4200 MHz | 5150 – 5925 MHz

Polarization ±45°

Electrical Specifications

Frequency Band, MHz	1695-1880	1850-1990	1920-2180	2300-2690	3300-4200	5150-5925
Gain, dBi	8.1	8.4	8.7	8.5	8.9	3.7
Beamwidth, Horizontal, degrees	360	360	360	360	360	360
Beamwidth, Vertical, degrees	18	17.1	16.2	15.4	31.5	22.4

ANDREW_®

VVSSP-360S-D

Beam Tilt, degrees	4	4	4	4	0	0
USLS (First Lobe), dB	17	13	12	12	7	4
Isolation, Cross Polarization, dB	25	25	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25	25	25
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153	-153	-140	
Input Power per Port at 50°C, maximum, watts	75	75	75	75	50	5

Mechanical Specifications

Effective Projective Area (EPA), frontal $0.1 \text{ m}^2 \mid 1.076 \text{ ft}^2$ Effective Projective Area (EPA), lateral $0.1 \text{ m}^2 \mid 1.076 \text{ ft}^2$

Wind Loading @ Velocity, frontal 102.0 N @ 150 km/h (22.9 lbf @ 150 km/h)

Wind Speed, maximum 241 km/h (150 mph)

Packaging and Weights

 Width, packed
 418 mm | 16.457 in

 Depth, packed
 404 mm | 15.906 in

 Length, packed
 888 mm | 34.961 in

 Weight, gross
 14.5 kg | 31.967 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance

