

Behind The Wall Pre-Radiused LC Connector for 0.9 mm Fiber, multimode, 100 bulk pack

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber connector |
| Product Brand | LazrSPEED® OptiSPEED® |

General Specifications

| | |
|-------------------------|--------------|
| Body Style | BTW |
| Color | Beige |
| Ferrule Geometry | Pre-radiused |
| Interface | LC/UPC |

Dimensions

| | |
|----------------------------------|-------------------|
| Length | 32 mm 1.26 in |
| Compatible Cable Diameter | 0.9 mm 0.035 in |

Material Specifications

| | |
|-------------------------|----------|
| Ferrule Material | Zirconia |
|-------------------------|----------|

Mechanical Specifications

| | |
|--|---------------|
| Cable Retention Strength, maximum | 1.00 lb @ 0 ° |
|--|---------------|

Optical Specifications

| | |
|---|------------------|
| Fiber Mode | Multimode |
| Insertion Loss Change, mating | 0.3 dB |
| Optical Components Standard | ANSI/TIA-568-C.3 |
| Insertion Loss Change, temperature | 0.3 dB |
| Insertion Loss, typical | 0.17 dB |
| Return Loss, minimum | 20 dB |

Packaging and Weights

760031393

Packaging quantity 100

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

* Footnotes

Insertion Loss Change, mating TIA-568: Maximum insertion loss change after 500 matings

Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)