


# 884019904/10 | CS340 BLK C6 4/24 U/UTP RL 1KFT



CS340 Category 6 U/UTP filled Cable, outdoor direct burial, black jacket, 4 pair count, 1000 ft (305 m) length, reel

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America
Portfolio	NETCONNECT®
Product Type	Twisted pair cable


## General Specifications

Product Number	CS340
ANSI/TIA Category	6
Cable Component Type	Horizontal
Cable Type	U/UTP (unshielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Jacket Color	Black
Note	All electrical transmission tests include swept frequency measurements
Pairs, quantity	4
Separator Type	Isolator
Transmission Standards	ANSI/TIA-568.2-D   CENELEC EN 50288-6-1   ISO/IEC 11801 Class E

## Dimensions

Cable Length	304.8 m   1000 ft
Diameter Over Jacket, nominal	6.223 mm   0.245 in
Jacket Thickness	0.635 mm   0.025 in
Conductor Gauge, singles	24 AWG

## Cross Section Drawing



Electrical Specifications

Characteristic Impedance	100 ohm
dc Resistance Unbalance, maximum	5 %
dc Resistance, maximum	9.38 ohms/100 m   2.859 ohms/100 ft
Delay Skew, maximum	45 ns
Dielectric Strength, minimum	1500 Vac   2500 Vdc
Mutual Capacitance at Frequency	6.0 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	65 %
Operating Frequency, maximum	250 MHz
Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A
Safety Voltage Rating	300 V

Electrical Cable Performance

CS	CommScope		
STD	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above		
TYP	Typical Electrical Performance		
IL	Insertion Loss (dB/100m)	NEXT	Near End Crosstalk (dB/100m)
ACR	Attenuation to Crosstalk Ratio (dB/100m)	PSNEXT	Power Sum Near End Crosstalk (db/100m)
PSACR	Power Sum Attenuation to Crosstalk Ratio (dB/100m)	ACRF	Attenuation to Crosstalk Ratio - Far End (dB/100m)
PSACRF	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)	RL	Return Loss (dB)
TCL	Transverse Conversion Loss (dB/100m)	ELTCTL	Equal Level Transverse Conversion Transfer Loss (dB/100m)

Freq. MHz	IL		NEXT		ACR		PSNEXT		PSACR		ACRF		PSACRF		RL		TCL	ELTCTL
	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	STD
1	2	1.7	74.3	90.1	72.3	88.4	72.3	88.2	70.3	86.5	67.8	85.2	64.8	83.7	20	30.6	40	35
4	3.8	3.4	65.3	81.3	61.5	77.9	63.3	79.4	59.5	76	55.8	73.5	52.8	72.1	23	29	40	23
8	5.3	4.8	60.8	77	55.4	72.1	58.8	74.9	53.4	70.1	49.7	67.6	46.7	66	24.5	31.6	40	16.9
10	6	5.4	59.3	74.9	53.3	69.5	57.3	73	51.3	67.6	47.8	65.7	44.8	64.1	25	32.7	40	15
16	7.6	6.9	56.2	71.7	48.7	64.8	54.2	69.7	46.7	62.8	43.7	61.6	40.7	59.9	25	34.8	38	10.9
20	8.5	7.7	54.8	69.5	46.3	61.8	52.8	67.7	44.3	60	41.8	59.6	38.8	57.9	25	35.8	37	9
25	9.5	8.6	53.3	67.8	43.8	59.2	51.3	66	41.8	57.4	39.8	57.6	36.8	55.9	24.3	35.6	36	7
31.25	10.7	9.6	51.9	66.7	41.2	57.1	49.9	64.9	39.2	55.2	37.9	55.6	34.9	53.8	23.6	35.6	35.1	
62.5	15.4	13.8	47.4	62.3	32	48.5	45.4	60.4	30	46.6	31.9	48.5	28.9	47	21.5	29.7	32	
100	19.8	17.7	44.3	58.8	24.5	41.1	42.3	57.1	22.5	39.4	27.8	42.5	24.8	41.5	20.1	26.1	30	
155	25.2	22.3	41.4	56.2	16.3	33.9	39.4	54.5	14.3	32.2	24	37.9	21	36.7	18.8	22.6	28.1	
200	29	25.6	39.8	54.2	10.8	28.6	37.8	52.6	8.8	27	21.8	36.5	18.8	35.3	18	20.5	27	
250	32.8	28.9	38.3	51.4	5.5	22.5	36.3	49.9	3.5	21	19.8	35.2	16.8	33.8	17.3	18.6	26	
300		31.9		49.4		17.5		48		16.1		31.9		30.7		17.3		
350		34.8		46.5		11.8		45.2		10.5		30.3		29		16.1		
400		37.3		44.3		7		43		5.7		29.1		27.7		15.1		
450		39.7		43.6		3.9		42.6		2.8		27.1		25.5		14.4		
500		42.3		42.8		0.5		41.7		-0.6		26.7		25		13.9		
550		44.7		42.6		-2.1		41.4		-3.3		25.1		23.6		13.4		
600		46.8		43.5		-3.4		42.3		-4.5		23.4		21.8		13.3		
650		49		43.7		-5.2		42.1		-6.9		22.8		20.7		12.9		

Material Specifications

Conductor Material	Bare copper
Insulation Material	Polyolefin
Jacket Material	PE
Separator Material	Polyolefin

Mechanical Specifications

Pulling Tension, maximum	11.34 kg   25 lb
--------------------------	------------------

Environmental Specifications

Installation temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Environmental Note	UV resistant for outdoor and/or direct burial installations
Environmental Space	Buried
Safety Standard	ANSI/ICEA S-107-704-2012

Packaging and Weights

Cable weight	39.288 kg/km   26.4 lb/kft
Packaging Type	Reel

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system