


2-599615-2 | C-006-CN-5K-M06AQ/28D/GY/D



Fiber Optic Cable, 6-fiber, OM4, 2000 m, aqua

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA

Portfolio

CommScope®

Product Type

Fiber indoor/outdoor cable

General Specifications

Cable Type

Loose tube

Fibers per Subunit, quantity

6

Filler, quantity

1

Jacket Color

Aqua

Subunit Type

Gel-free

Total Fiber Count

6

Dimensions


Cable Length

2000 m | 6,561.68 ft

Diameter Over Jacket

6.4 mm | 0.252 in

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded	139.7 mm 5.5 in
Minimum Bend Radius, unloaded	129.5 mm 5.098 in
Tensile Load, long term, maximum	650 N 146.126 lbf
Tensile Load, short term, maximum	1250 N 281.011 lbf

Optical Specifications

Fiber Type	OM4
-------------------	-----

Optical Specifications, Wavelength Specific

Attenuation, maximum	1.00 dB/km @ 1,300 nm 3.50 dB/km @ 850 nm
Standards Compliance	IEC 60794-1 TIA-492AAAD (OM4)

Environmental Specifications

Installation temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Operating Temperature	-10 °C to +70 °C (+14 °F to +158 °F)
Storage Temperature	-10 °C to +70 °C (+14 °F to +158 °F)
EN50575 CPR Cable EuroClass Fire Performance	Dca
EN50575 CPR Cable EuroClass Smoke Rating	s2
EN50575 CPR Cable EuroClass Droplets Rating	d2
EN50575 CPR Cable EuroClass Acidity Rating	a1

2-599615-2 | C-006-CN-5K-M06AQ/28D/GY/D

Environmental Space

Universal Low Smoke Zero Halogen (ULSZH)

Packaging and Weights

Cable weight

47 kg/km | 31.583 lb/kft

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant



* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable