
## 760248185 | P-096-MP-5K-F08AQ/20T



Fiber indoor cable, LazrSPEED® Plenum MPO Trunk, 96 fiber multi-unit with 8 fiber subunits, Multimode OM4, Gel-free, Feet jacket marking, Aqua jacket color

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | Latin America | Middle East

/Africa | North America

Portfolio CommScope®

Product Type Fiber indoor cable

**Product Series** P-MP

### General Specifications

Cable Type MPO trunk cable

Construction Type Non-armored

**Subunit Type** Gel-free

Jacket Color Aqua

Jacket Marking Feet

Subunit, quantity 12

Fibers per Subunit, quantity 8

**Total Fiber Count** 96

#### **Dimensions**

Buffer Tube/Subunit Diameter 2 mm | 0.079 in

**Diameter Over Jacket** 11.8 mm | 0.465 in

## Representative Image



# 760248185 | P-096-MP-5K-F08AQ/20T



### Mechanical Specifications

Minimum Bend Radius, loaded 172 mm | 6.772 in

Minimum Bend Radius, unloaded 115 mm | 4.528 in

**Tensile Load, long term, maximum** 200 N | 44.962 lbf

**Tensile Load, short term, maximum** 667 N | 149.948 lbf

**Compression** 10 N/mm | 57.101 lb/in

**Compression Test Method** FOTP-41 | IEC 60794-1 E3

Flex 300 cycles

FIEX Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 0.74 N-m | 6.55 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 500 m | 1,640.42 ft

Optical Specifications

Fiber Type OM4, LazrSPEED® 550 | OM4, LazrSPEED® 550

### **Environmental Specifications**

Installation temperature  $0 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$ Operating Temperature  $0 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (+32 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$ Storage Temperature  $-40 \, ^{\circ}\text{C} \, \text{to} + 70 \, ^{\circ}\text{C} \, (-40 \, ^{\circ}\text{F} \, \text{to} + 158 \, ^{\circ}\text{F})$ 

Page 2 of 3



# 760248185 | P-096-MP-5K-F08AQ/20T

Cable Qualification Standards ANSI/ICEA S-83-596 | Telcordia GR-409

Environmental Space Plenum

Flame Test Listing

NEC OFNP (ETL) and c(ETL)

Flame Test Method

NFPA 130 | NFPA 262

**Environmental Test Specifications** 

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

Heat Age Test Method IEC 60794-1 F9

**Low High Bend** 0 °C to +70 °C (+32 °F to +158 °F)

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $0 \,^{\circ}\text{C to } +70 \,^{\circ}\text{C (+32 °F to } +158 \,^{\circ}\text{F)}$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 143 kg/km | 96.092 lb/kft

#### Included Products

CS-5K-MP – LazrSPEED® 550 OM4 Bend-Insensitive Multimode

Fiber

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

