



M-Series Modular Jack, RJ45, Cat6 Unshielded, Violet

OBSOLETE

This product was discontinued on: November 30, 2024

Replaced By:

760258944
UNJ600T-VI

M-Series Modular Jack, RJ45, Cat6 Unshielded, Violet

Product Classification

Regional Availability	North America
Portfolio	Uniprise®
Product Type	Modular jack
Product Series	UNJ Series

General Specifications

ANSI/TIA Category	6
Application	Universal design and label supports both T568 A and B wiring
Cable Type	Unshielded
Color	Violet
Conductor Type	Solid Stranded
Integrated Dust Cover Type	None
Mounting	M Series faceplates, surface mount boxes, consolidation point boxes, or CommScope modular panels
Mounting Note	Can be mounted either at 90° (straight) or at 45° (angled) in any CommScope faceplate
Termination Type	IDC
Wiring	T568A T568B

Dimensions

Height	20.32 mm 0.8 in
Width	20.32 mm 0.8 in
Depth	30.48 mm 1.2 in
Compatible Conductor Gauge, solid	22 AWG 24 AWG
Compatible Conductor Gauge, stranded	22 AWG 23 AWG 24 AWG

Electrical Specifications

Contact Resistance Variation, maximum	20 mOhm
Contact Resistance, maximum	100 mOhm
Current Rating at Temperature	1.5 A @ 20 °C 1.5 A @ 68 °F
Dielectric Withstand Voltage, RMS, conductive surface	1,500 Vac @ 60 Hz
Dielectric Withstand Voltage, RMS, contact-to-contact	1,000 Vac @ 60 Hz
Insulation Resistance, minimum	500 MOhm
PoE Durability	Supports IEEE 802.3bt Type 4 (90 W) applications greater than 3000 plug to jack mating cycles

Material Specifications

Contact Plating Material	Precious metals
Material Type	Copper alloy High-impact, flame retardant, thermoplastic
Termination Contact Plating	Nickel

Mechanical Specifications

Plug Retention Force, minimum	133 N 29.9 lbf
Plug to Jack Mating Cycles	Complies to IEC 60603-7 series

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	UL cUL

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system