

Fiber OSP cable, LightScope® ZWP Single Jacket/Single Armor, High Fiber Count, , 336 fiberGel-Filled, Stranded Loose Tube, Singlemode G. 652.D and G.657.A1, Feet jacket marking, Black jacket color

- Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection
- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

#### Product Classification

| Regional Availability        | Asia   Australia/New Zealand   EMEA   Latin America   North<br>America |
|------------------------------|--|
| Portfolio                    | CommScope®   |
| Product Type                 | Fiber OSP cable  |
| Product Series               | O-LA   |
| Government Requirements      | Build America Buy America (BABA) compliant*                            |
| General Specifications       |  |
| Armor Type                   | Corrugated steel   |
| Cable Type                   | Stranded loose tube  |
| Construction Type            | Armored  |
| Subunit Type                 | Gel-filled   |
| Filler, quantity             | 4  |
| Jacket Color                 | Black  |
| Jacket Marking               | Feet   |
| Location of Manufacturing    | Claremont, North Carolina  |
| Subunit, quantity            | 14   |
| Fibers per Subunit, quantity | 24   |
| Total Fiber Count            | 336  |
| Dimensions                   |  |

Buffer Tube/Subunit Diameter

3.5 mm | 0.138 in

Page 1 of 4


©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2025



#### **Diameter Over Jacket**

22.9 mm | 0.902 in

# Representative Image



ΡE

### Material Specifications

Jacket Material

## Mechanical Specifications

| Minimum Bend Radius, loaded       | 344 mm   13.543 in                    |
|-----------------------------------|---------------------------------------|
| Minimum Bend Radius, unloaded     | 229 mm   9.016 in                     |
| Tensile Load, long term, maximum  | 800 N   179.847 lbf                   |
| Tensile Load, short term, maximum | 2700 N   606.984 lbf                  |
| Compression                       | 44 N/mm   251.246 lb/in               |
| Compression Test Method           | FOTP-41   IEC 60794-1 E3              |
| Flex                              | 25 cycles                             |
| Flex Test Method                  | FOTP-104   IEC 60794-1 E6             |
| Impact                            | 7.35 N-m   65.053 in lb               |
| Impact Test Method                | FOTP-25   IEC 60794-1 E4              |
| Strain                            | See long and short term tensile loads |
| Strain Test Method                | FOTP-33   IEC 60794-1 E1              |
| Twist                             | 10 cycles                             |
| Twist Test Method                 | FOTP-85   IEC 60794-1 E7              |
| Vertical Rise, maximum            | 228 m   748.032 ft                    |
|                                   |                                       |

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2025



**COMMSCOPE**<sup>®</sup>

### **Optical Specifications**

Fiber Type

G.652.D and G.657.A1 | G.652.D and G.657.A1

### **Environmental Specifications**

| Installation temperature      | -30 °C to +70 °C (-22 °F to +158 °F) |
|-------------------------------|--------------------------------------|
| Operating Temperature         | -40 °C to +70 °C (-40 °F to +158 °F) |
| Storage Temperature           | -40 °C to +75 °C (-40 °F to +167 °F) |
| Cable Qualification Standards | ANSI/ICEA S-87-640   EN 187105       |
| Environmental Space           | Aerial, lashed   Buried              |
| Jacket UV Resistance          | UV stabilized                        |
| Water Penetration             | 24 h                                 |
| Water Penetration Test Method | FOTP-82   IEC 60794-1 F5             |

### **Environmental Test Specifications**

| Cable Freeze                  | -2 °C   28.4 °F                      |
|-------------------------------|--------------------------------------|
| Cable Freeze Test Method      | FOTP-98   IEC 60794-1 F15            |
| Drip                          | 70 °C   158 °F                       |
| Drip Test Method              | FOTP-81   IEC 60794-1 E14            |
| Heat Age                      | -40 °C to +85 °C (-40 °F to +185 °F) |
| Heat Age Test Method          | IEC 60794-1 F9                       |
| Low High Bend                 | -30 °C to +60 °C (-22 °F to +140 °F) |
| Low High Bend Test Method     | FOTP-37   IEC 60794-1 E11            |
| Temperature Cycle             | -40 °C to +70 °C (-40 °F to +158 °F) |
| Temperature Cycle Test Method | FOTP-3   IEC 60794-1 F1              |
|                               |                                      |

#### Packaging and Weights

#### Cable weight

358 kg/km | 240.565 lb/kft

## Regulatory Compliance/Certifications

#### Class

ISO 9001:2015

Agency

Classification

:2015 Designed, manufactured and/or distributed under this quality management system

## Included Products

Page 3 of 4

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2025



DB-8W-LT – LightScope® ZWP Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

Page 4 of 4

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2025

