

Fiber OSP cable, LightScope® ZWP Single Jacket All-Dielectric, High Fiber Count, 312 fiber, Gel-Filled, Stranded Loose Tube, Singlemode G. 652.D and G.657.A1, Feet jacket marking, Black jacket color

 *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification


Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	O-LN
Government Requirements	Build America Buy America (BABA) compliant*
General Specifications	
Cable Type	Stranded loose tube
Construction Type	Non-armored
Subunit Type	Gel-filled
Filler, quantity	5
Jacket Color	Black
Jacket Marking	Feet
Location of Manufacturing	Claremont, North Carolina
Subunit, quantity	13
Fibers per Subunit, quantity	24
Total Fiber Count	312
Dimensions	
Buffer Tube/Subunit Diameter	3.5 mm 0.138 in
Diameter Over Jacket	21.5 mm 0.846 in

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2025



COMMSCOPE[®]

Representative Image



Material Specifications

Jacket Material

ΡE

Mechanical Specifications

Minimum Bend Radius, loaded	323 mm 12.717 in	
Minimum Bend Radius, unloaded	215 mm 8.465 in	
Tensile Load, long term, maximum	800 N 179.847 lbf	
Tensile Load, short term, maximum	2700 N 606.984 lbf	
Compression	22 N/mm 125.623 lb/in	
Compression Test Method	FOTP-41 IEC 60794-1 E3	
Flex	25 cycles	
Flex Test Method	FOTP-104 IEC 60794-1 E6	
Impact	6.62 N-m 58.592 in lb	
Impact Test Method	FOTP-25 IEC 60794-1 E4	
Strain	See long and short term tensile loads	
Strain Test Method	FOTP-33 IEC 60794-1 E1	
Twist	10 cycles	
Twist Test Method	FOTP-85 IEC 60794-1 E7	
Vertical Rise, maximum	317 m 1,040.026 ft	

Optical Specifications

Fiber Type

G.652.D and G.657.A1 | G.652.D and G.657.A1

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2025



Page 2 of 7

Environmental Specifications

Installation temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Cable Qualification Standards	ANSI/ICEA S-87-640 EN 187105
Environmental Space	Aerial, lashed Buried
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	FOTP-82 IEC 60794-1 F5

Environmental Test Specifications

-2 °C 28.4 °F	
FOTP-98 IEC 60794-1 F15	
70 °C 158 °F	
FOTP-81 IEC 60794-1 E14	
-40 °C to +85 °C (-40 °F to +185 °F)	
IEC 60794-1 F9	
-30 °C to +60 °C (-22 °F to +140 °F)	
FOTP-37 IEC 60794-1 E11	
-40 °C to +70 °C (-40 °F to +158 °F)	
FOTP-3 IEC 60794-1 F1	

Packaging and Weights

Cable weight

258 kg/km | 173.368 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Included Products

DB-8W-LT – LightScope® ZWP Singlemode Fiber

* Footnotes

Page 3 of 7

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2025



Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 4 of 7

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 6, 2025



LightScope® ZWP Singlemode Fiber

LightScope[®] 2000

Product Classification

Portfolio	CommScope®	
Product Type	Optical fiber	
General Specifications		
Cladding Diameter	125 µm	
Cladding Diameter Tolerance	±0.7 μm	
Cladding Non-Circularity, maximum	0.7 %	
Coating Diameter (Colored)	249 µm	
Coating Diameter (Uncolored)	242 µm	
Coating Diameter Tolerance (Colored)	±13 μm	
Coating Diameter Tolerance (Uncolored)	±5 μm	
Coating/Cladding Concentricity Error, maximum	12 µm	
Core Diameter	8.3 µm	
Core/Clad Offset, maximum	0.5 μm	
Proof Tensile Stress	100,000 psi (0.69 GPa)	
Dimensions		
Fiber Curl, minimum	num 4 m 13.123 ft	
Mechanical Specifications		
Macrobending, 20 mm Ø mandrel, 1 turn	0.75 dB @ 1,550 nm 1.50 dB @ 1,625 nm	
Macrobending, 30 mm Ø mandrel, 10 turns	0.25 dB @ 1,550 nm 1.00 dB @ 1,625 nm	
Macrobending, 60 mm Ø mandrel, 100 turns	0.05 dB @ 1,550 nm 0.05 dB @ 1,625 nm	
Coating Strip Force, maximum	8.9 N 2.001 lbf	
Coating Strip Force, minimum	1.3 N 0.292 lbf	
Dynamic Fatigue Parameter, minimum	20	

Page 5 of 7

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 30, 2025



DB-8W-LT

Optical Specifications

Cabled Cutoff Wavelength, maximum	1260 nm
Point Defects, maximum	0.1 dB
Zero Dispersion Slope, maximum	0.092 ps/[km-nm-nm]
Zero Dispersion Wavelength, maximum	1324 nm
Zero Dispersion Wavelength, minimum	1300 nm
Optical Specifications, Wavelength Specific	
Attenuation, maximum	0.22 dB/km @ 1,550 nm 0.25 dB/km @ 1,490 nm 0.25 dB/km @ 1,625 nm 0.36 dB/km @ 1,310 nm 0.36 dB/km @ 1,385 nm
Attenuation, typical	0.19 dB/km @ 1,550 nm 0.33 dB/km @ 1,310 nm
Backscatter Coefficient	-79.6 dB @ 1,310 nm -82.1 dB @ 1,550 nm
Dispersion, maximum	18 ps(nm-km) at 1550 nm 3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310 nm
Index of Refraction	1.467 @ 1,310 nm 1.467 @ 1,385 nm 1.468 @ 1,550 nm
Mode Field Diameter	10.4 μm @ 1,550 nm 9.2 μm @ 1,310 nm 9.6 μm @ 1,385 nm
Mode Field Diameter Tolerance	±0.4 μm @ 1310 nm ±0.5 μm @ 1550 nm ±0.6 μm @ 1385 nm
Polarization Mode Dispersion Link Design Value, maximum	0.04 ps/sqrt(km)
Standards Compliance	ITU-T G.652.D ITU-T G.657.A1

Environmental Specifications

Heat Aging, maximum	0.05 dB/km @ 85 °C
Temperature Dependence, maximum	0.05 dB/km
Temperature Humidity Cycling, maximum	0.05 dB/km
Water Immersion, maximum	0.05 dB/km @ 23 °C

Regulatory Compliance/Certifications

Classification

Agency

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

* Footnotes

Page 6 of 7

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 30, 2025

COMMSCOPE°

DB-8W-LT

Temperature Dependence, maximumTemperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)Temperature Humidity Cycling, maximumTemperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

Page 7 of 7

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 30, 2025

