

Fiber outdoor drop cable, LightScope® ZWP Self-Supporting All-Dielectric, Singlemode G.652.D and G.657.Al, 12 fiber Arid Core construction, Gel-filled, central loose tube, Meter jacket marking, Black jacket color

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber drop cable

**Product Series** O-DF

General Specifications

Cable Type Central loose tube

Construction Type Non-armored

Subunit TypeGel-filledJacket ColorBlack

Jacket Marking Method Inkjet

Jacket Marking Text COMMSCOPE GB 8107990/DB F.O. CABLE 12 X 9/125 G652D

/G657A1 MDPE 20T (serial number) (meter mark)

Subunit, quantity 1

Fibers per Subunit, quantity 12

**Total Fiber Count** 12

**Dimensions** 


Height Over Jacket 4.5 mm | 0.177 in

Buffer Tube/Subunit Diameter 3 mm | 0.118 in

Diameter Over Jacket 7.9 mm | 0.311 in

Representative Image





### Material Specifications

Jacket Material PE

### Mechanical Specifications

Minimum Bend Radius, loaded86 mm | 3.386 inMinimum Bend Radius, unloaded81 mm | 3.189 inTensile Load, long term, maximum400 N | 89.924 lbf

Tensile Load, short term, maximum 1334 N | 299.895 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method FOTP-41 | IEC 60794-1 E3

Flex 35 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

 Impact
 2.94 N-m | 26.021 in lb

 Impact Test Method
 FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 1047 m | 3,435.039 ft

**Optical Specifications** 



**Fiber Type** G.652.D and G.657.A1 | G.652.D and G.657.A1

#### **Environmental Specifications**

Installation temperature  $-30 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C } (-22 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$ Operating Temperature  $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C } (-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F})$ Storage Temperature  $-40 \,^{\circ}\text{C to} + 75 \,^{\circ}\text{C } (-40 \,^{\circ}\text{F to} + 167 \,^{\circ}\text{F})$ 

Cable Qualification StandardsANSI/ICEA S-110-717

Environmental Space Aerial, self-support | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method FOTP-82 | IEC 60794-1 F5

#### **Environmental Test Specifications**

**Cable Freeze** -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

**Drip** 70 °C | 158 °F

**Drip Test Method** FOTP-81 | IEC 60794-1 E14

-40 °C to +85 °C (-40 °F to +185 °F)

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend**  $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$ 

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $-40 \,^{\circ}\text{C to} + 70 \,^{\circ}\text{C} \left(-40 \,^{\circ}\text{F to} + 158 \,^{\circ}\text{F}\right)$ 

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 39 kg/km | 26.207 lb/kft

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant







#### Included Products

CS-8W-250-EMEA – LightScope® ZWP Singlemode Fiber 250um

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

