

Fiber OSP cable, Outdoor Steel Armored, Gel-Filled Central Tube Ribbon, 288 fiber, Singlemode G.652.D and G.657.A1, Feet jacket marking, Black jacket color

OBSOLETE

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	O-CA


General Specifications

Armor Type	Corrugated steel
Cable Type	Ribbon central tube
Construction Type	Armored
Subunit Type	Gel-filled
Fibers per Ribbon, quantity	24
Jacket Color	Black
Jacket Marking	Feet
Total Fiber Count	288

Dimensions

Cable Length	5445 m   17,864.174 ft
Buffer Tube/Subunit Diameter	14.3 mm   0.563 in
Diameter Over Jacket	21.4 mm   0.843 in

Representative Image



Mechanical Specifications

Minimum Bend Radius, loaded	428 mm   16.85 in
Minimum Bend Radius, storage coils	321 mm   12.638 in
Minimum Bend Radius, unloaded	214 mm   8.425 in
Tensile Load, long term, maximum	800 N   179.847 lbf
Tensile Load, short term, maximum	2700 N   606.984 lbf
Compression	22 N/mm   125.623 lb/in
Compression Test Method	FOTP-41   IEC 60794-1 E3
Flex	25 cycles
Flex Test Method	FOTP-104   IEC 60794-1 E6
Impact	4.4 N-m   38.943 in lb
Impact Test Method	FOTP-25   IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1 E7

Optical Specifications

Fiber Type	G.652.D and G.657.A1   G.652.D and G.657.A1
------------	---

Environmental Specifications

Installation temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Cable Qualification Standards	ANSI/ICEA S-87-640   Telcordia GR-20
Environmental Space	Aerial, lashed   Buried
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	FOTP-82   IEC 60794-1 F5

Environmental Test Specifications

Drip	70 °C   158 °F
Drip Test Method	FOTP-81
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)
Low High Bend Test Method	FOTP-37   IEC 60794-1 E11
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1 F1

Packaging and Weights

Cable weight	459 kg/km   308.434 lb/kft
--------------	----------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



Included Products

# 810009566/DB | O-288-CA-RB-F24NS/8Z/93B

---

CS-8Z-RB-OUTDOOR – Low Water Peak Dispersion-Unshifted OS2 Singlemode Fiber

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

# CS-8Z-RB-OUTDOOR

Low Water Peak Dispersion-Unshifted OS2 Singlemode Fiber

## Product Classification

Portfolio	CommScope®
Product Type	Optical fiber

## General Specifications

Cladding Diameter	125 µm
Cladding Diameter Tolerance	±0.7 µm
Cladding Non-Circularity, maximum	1 %
Coating Diameter (Colored)	250 µm
Coating Diameter (Uncolored)	245 µm
Coating Diameter Tolerance (Colored)	±15 µm
Coating Diameter Tolerance (Uncolored)	±10 µm
Coating/Cladding Concentricity Error, maximum	12 µm
Core/Clad Offset, maximum	0.5 µm
Proof Test	689.476 N/mm²   100000 psi

## Dimensions

Fiber Curl, minimum	4 m   13.123 ft
---------------------	-----------------

## Mechanical Specifications

Macrobending, 20 mm Ø mandrel, 1 turn	0.75 dB @ 1,550 nm   1.50 dB @ 1,625 nm
Macrobending, 30 mm Ø mandrel, 10 turns	0.25 dB @ 1,550 nm   1.00 dB @ 1,625 nm
Macrobending, 60 mm Ø mandrel, 100 turns	0.03 dB @ 1,550 nm   0.03 dB @ 1,625 nm
Coating Strip Force, maximum	8.9 N   2.001 lbf
Coating Strip Force, minimum	1.3 N   0.292 lbf
Dynamic Fatigue Parameter, minimum	18

## Optical Specifications

Cabled Cutoff Wavelength, maximum	1260 nm
Point Defects, maximum	0.1 dB
Zero Dispersion Slope, maximum	0.092 ps/[km-nm-nm]

# CS-8Z-RB-OUTDOOR

Zero Dispersion Wavelength, maximum	1324 nm
Zero Dispersion Wavelength, minimum	1300 nm
Optical Specifications, Wavelength Specific	
Attenuation, maximum	0.25 dB/km @ 1,550 nm   0.35 dB/km @ 1,310 nm   0.35 dB/km @ 1,385 nm
Backscatter Coefficient	-79.6 dB @ 1,310 nm   -82.1 dB @ 1,550 nm
Dispersion, maximum	18 ps(nm-km) at 1550 nm   3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310 nm
Index of Refraction	1.467 @ 1,310 nm   1.468 @ 1,385 nm   1.468 @ 1,550 nm
Mode Field Diameter	10.4 µm @ 1,550 nm   9.2 µm @ 1,310 nm   9.6 µm @ 1,385 nm
Mode Field Diameter Tolerance	±0.4 µm @ 1310 nm   ±0.5 µm @ 1550 nm   ±0.6 µm @ 1385 nm
Polarization Mode Dispersion Link Design Value, maximum	0.2 ps/sqrt(km)
Standards Compliance	ITU-T G.652.D   ITU-T G.657.A1   TIA-492CAAB (OS2)

## Environmental Specifications

Heat Aging, maximum	0.05 dB/km @ 85 °C
Temperature Dependence, maximum	0.05 dB/km
Temperature Humidity Cycling, maximum	0.05 dB/km
Water Immersion, maximum	0.05 dB/km @ 23 °C

## Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



### \* Footnotes

Temperature Dependence, maximum	Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)
Temperature Humidity Cycling, maximum	Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity