

Fiber OSP cable, LightScope® ZWP Single Jacket/Single Armor, Gel-Filled, Central Tube Cable, 24 fibers, Singlemode G.652.D and G.657.A1, Feet jacket marking, Black jacket color

- Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection
- \*Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

#### Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

 Portfolio
 CommScope®

 Product Type
 Fiber OSP cable

Product Series O-CA

Government Requirements Build America Buy America (BABA) compliant\*

General Specifications

Armor Type Corrugated steel

Cable Type Central loose tube

Construction TypeArmoredSubunit TypeGel-filledJacket ColorBlack

Jacket Marking Feet

**Location of Manufacturing**Claremont, North Carolina

Fibers per Subunit, quantity 12


Total Fiber Count 24

Dimensions

Buffer Tube/Subunit Diameter4 mm | 0.157 inDiameter Over Jacket11 mm | 0.433 in



#### Representative Image



### Material Specifications

Jacket Material PE

#### Mechanical Specifications

Minimum Bend Radius, loaded165 mm | 6.496 inMinimum Bend Radius, unloaded110 mm | 4.331 inTensile Load, long term, maximum800 N | 179.847 lbfTensile Load, short term, maximum2700 N | 606.984 lbf

 Compression
 44 N/mm | 251.246 lb/in

 Compression Test Method
 FOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

Twist Test Method FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 608 m | 1,994.751 ft

**Optical Specifications** 

**Fiber Type** G.652.D and G.657.A1 | G.652.D and G.657.A1

**COMMSCOPE®** 

#### **Environmental Specifications**

Installation temperature

-30 °C to +70 °C (-22 °F to +158 °F)

Operating Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

Storage Temperature

-40 °C to +75 °C (-40 °F to +167 °F)

Cable Qualification Standards

ANSI/ICEA S-87-640 | EN 187105

Environmental Space Aerial, lashed | Buried

Jacket UV Resistance UV stabilized

Water Penetration 24 h

**Water Penetration Test Method** FOTP-82 | IEC 60794-1 F5

**Environmental Test Specifications** 

**Cable Freeze** -2 °C | 28.4 °F

Cable Freeze Test Method FOTP-98 | IEC 60794-1 F15

**Drip** 70 °C | 158 °F

**Drip Test Method** FOTP-81 | IEC 60794-1 E14

**Heat Age** -40 °C to +85 °C (-40 °F to +185 °F)

**Heat Age Test Method** IEC 60794-1 F9

Low High Bend -30 °C to +60 °C (-22 °F to +140 °F)

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle** -40 °C to +70 °C (-40 °F to +158 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

**Cable weight** 134 kg/km | 90.044 lb/kft

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

DB-8W-LT - LightScope® ZWP Singlemode

Fiber



#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable