

Fiber indoor/outdoor cable, LightScope® ZWP, Mini Single Jacket, All-Dielectric, Low Smoke Zero Halogen (LSZH), Singlemode G.652.D and G. 657.A1, 72 fiber, Gel-Filled, Stranded Loose Tube, Feet jacket marking, Black jacket color, Eca flame rating


Product Classification

Designal Availability	
Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber indoor/outdoor cable
Product Series	C-LN
General Specifications	
Cable Type	Stranded loose tube
Construction Type	Non-armored
Subunit Type	Gel-filled
Jacket Color	Black
Jacket Marking	Meters
Jacket Marking Method	Inkjet
Jacket Marking Text	COMMSCOPE GB OPTICAL CABLE OS2 SM 72 FIBER EN50575 CLASS E [SERIAL NUMBER] [MM/YY] [METRE MARK]
Subunit, quantity	6
Fibers per Subunit, quantity	12
Total Fiber Count	72
Dimensions	
Buffer Tube/Subunit Diameter	2 mm 0.079 in
Diameter Over Jacket	11 mm 0.433 in

Representative Image

Page 1 of 4





Mechanical Specifications

Minimum Bend Radius, loaded	165 mm 6.496 in
Minimum Bend Radius, unloaded	110 mm 4.331 in
Tensile Load, long term, maximum	800 N 179.847 lbf
Tensile Load, short term, maximum	2700 N 606.984 lbf
Compression	22 N/mm 125.623 lb/in
Compression Test Method	IEC 60794-1 E3
Flex	25 cycles
Flex Test Method	IEC 60794-1 E6
Impact	10 N-m 88.507 in lb
Impact Test Method	IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	IEC 60794-1 E7
Vertical Rise, maximum	643 m 2,109.58 ft
Optical Specifications	
Fiber Type	G.652.D and G.657.A1, TeraSPEED® OS2 OS2

Environmental Specifications

Installation temperature	-30 °C to +60 °C (-22 °F to +140 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Page 2 of 4



Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Cable Qualification Standards	EN 187105 IEC 60794-1-2
EN50575 CPR Cable EuroClass Fire Performance	Eca
Environmental Space	Aerial, lashed Buried Low Smoke Zero Halogen (LSZH)
Flame Test Method	IEC 60332-1-2 IEC 60754-2 IEC 61034-2
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	IEC 60794-1 F5

Environmental Test Specifications

Cable Freeze	-2 °C 28.4 °F
Cable Freeze Test Method	IEC 60794-1 F15
Drip	70 °C 158 °F
Drip Test Method	IEC 60794-1 E14
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)
Low High Bend Test Method	IEC 60794-1 E11
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	IEC 60794-1 F1

Packaging and Weights

Cable weight

127 kg/km | 85.34 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 3 of 4



Included Products

CS-8W-250-EMEA – LightScope® ZWP Singlemode Fiber 8W-250um

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 4 of 4

