
# 860646609/DB | 0-006-LA-8G-M06NS/20G



Fiber OSP cable, LightScope® ZWP Mini Single Jacket/Single Armor, 6 fiber, Gel-Filled, Stranded Loose Tube, Singlemode G.657.A2, Meters jacket marking, Black jacket color

 Corrugated steel tape armor is strong yet flexible, providing additional crush and rodent protection


Product Classification	
Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	O-LA
General Specifications	
Armor Type	Corrugated steel
Cable Type	Stranded loose tube
Construction Type	Armored
Subunit Type	Gel-filled
Filler, quantity	5
Jacket Color	Black
Jacket Marking	Meters
Jacket Marking Method	Inkjet
Jacket Marking Text	COMMSCOPE GB OPTICAL CABLE TYPE G657A2 SM 6 FIBER [SERIAL NUMBER] [MM /YYYY] [METRE MARK]
Subunit, quantity	1
Fibers per Subunit, quantity	6
Total Fiber Count	6
Dimensions	
Buffer Tube/Subunit Diameter	2 mm   0.079 in
Diameter Over Jacket	10.8 mm   0.425 in

Page 1 of 6



# 860646609/DB | 0-006-LA-8G-M06NS/20G

### Representative Image



#### Material Specifications

Material Specifications	
Jacket Material	PE
Mechanical Specifications	
Minimum Bend Radius, loaded	162 mm   6.378 in
Minimum Bend Radius, unloaded	108 mm   4.252 in
Tensile Load, long term, maximum	800 N   179.847 lbf
Tensile Load, short term, maximum	2700 N   606.984 lbf
Compression	44 N/mm   251.246 lb/in
Compression Test Method	IEC 60794-1 E3
Flex	25 cycles
Flex Test Method	IEC 60794-1 E6
Impact	10 N-m   88.507 in lb
Impact Test Method	IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	IEC 60794-1 E7
Vertical Rise, maximum	672 m   2,204.724 ft
Ontical Specifications	

### **Optical Specifications**

Fiber Type

G.657.A2 | G.657.A2, TeraSPEED®

Page 2 of 6



### **Environmental Specifications**

Installation temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +75 °C (-40 °F to +167 °F)
Cable Qualification Standards	ANSI/ICEA S-87-640   EN 187105   IEC 60794-1-2
Environmental Space	Aerial, lashed   Buried
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	IEC 60794-1 F5

### **Environmental Test Specifications**

Cable Freeze	-2 °C   28.4 °F
Cable Freeze Test Method	IEC 60794-1 F15
Drip	70 °C   158 °F
Drip Test Method	IEC 60794-1 E14
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)
Low High Bend Test Method	IEC 60794-1 E11
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	IEC 60794-1 F1

### Packaging and Weights

#### Cable weight

122 kg/km | 81.98 lb/kft

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

Page 3 of 6



# 860646609/DB | 0-006-LA-8G-M06NS/20G



#### Included Products

CS-8G-LT

Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G.657.A2, B2)

### \* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

Page 4 of 6



## CS-8G-LT

Enhanced Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber (ITU-T G. 657.A2, B2)

#### Product Classification

Portfolio	CommScope®
Product Type	Optical fiber
	option hoef
General Specifications	
Cladding Diameter	125 µm
Cladding Diameter Tolerance	±0.7 μm
Cladding Non-Circularity, maximum	0.7 %
Coating Diameter (Colored)	249 µm
Coating Diameter (Uncolored)	242 µm
Coating Diameter Tolerance (Colored)	±13 µm
Coating Diameter Tolerance (Uncolored)	±5 μm
Coating/Cladding Concentricity Error, maximum	12 µm
Core/Clad Offset, maximum	0.5 µm
Proof Test	689.476 N/mm²   100000 psi
Dimensions	
Fiber Curl, minimum	4 m   13.123 ft
Mechanical Specifications	
Macrobending, 15 mm Ø mandrel, 1 turn	0.50 dB @ 1,550 nm   1.00 dB @ 1,625 nm
Macrobending, 20 mm Ø mandrel, 1 turn	0.10 dB @ 1,550 nm   0.20 dB @ 1,625 nm
Macrobending, 30 mm Ø mandrel, 10 turns	0.03 dB @ 1,550 nm   0.10 dB @ 1,625 nm
Coating Strip Force, maximum	8.9 N   2.001 lbf
Coating Strip Force, minimum	1.3 N   0.292 lbf
Dynamic Fatigue Parameter, minimum	20
Optical Specifications	
Cabled Cutoff Wavelength, maximum	1260 nm
Point Defects, maximum	0.1 dB

Page 5 of 6



# CS-8G-LT

Zero Dispersion Slope, maximum	0.092 ps/[km-nm-nm]
Zero Dispersion Wavelength, maximum	1324 nm
Zero Dispersion Wavelength, minimum	1302 nm
Optical Specifications, Wavelength Specific	
Attenuation, maximum	0.25 dB/km @ 1,550 nm   0.33 dB/km @ 1,385 nm   0.36 dB/km @ 1,310 nm
Dispersion, maximum	18 ps(nm-km) at 1550 nm ( 3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310 nm
Index of Refraction	1.467 @ 1,310 nm   1.467 @ 1,385 nm   1.468 @ 1,550 nm
Mode Field Diameter	8.6 μm @ 1,310 nm   9.8 μm @ 1,550 nm
Mode Field Diameter Tolerance	±0.4 μm @ 1310 nm   ±0.5 μm @ 1550 nm
Polarization Mode Dispersion Link Design Value, maximum	0.06 ps/sqrt(km)
Standards Compliance	ITU-T G.657.A2   ITU-T G.657.B2

### Environmental Specifications

Heat Aging, maximum	0.05 dB/km @ 85 °C
Temperature Dependence, maximum	0.05 dB/km
Temperature Humidity Cycling, maximum	0.05 dB/km
Water Immersion, maximum	0.05 dB/km @ 23 °C

### Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

### \* Footnotes

Temperature Dependence, maximum	Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)
Temperature Humidity Cycling, maximum	Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F) up to 95% relative humidity

Page 6 of 6

