


884021358/16 | CS54ZC WHT C7 4/23 S/FTP RL

500M



CS54ZC Category 7 S/FTP Cable, low smoke zero halogen, white jacket, 4 pair count, 1640 ft (500 m) length, reel

OBSOLETE

This product was discontinued on: October 1, 2024

Replaced By:

884010858/16

CS54ZB Category 7 S/FTP Cable, low smoke zero halogen, white jacket, 4 pair count,
CS54ZB WHT C7 4/23 S/FTP RL 500M 1640 ft (500 m) length, reel

Product Classification

Regional Availability	EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair cable

General Specifications


Product Number	CS54ZC
ANSI/TIA Category	7
Cable Component Type	Horizontal
Cable Type	S/FTP (shielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Jacket Color	White
Note	All electrical transmission tests include swept frequency measurements
Pairs, quantity	4
Transmission Standards	CENELEC EN 50288-4-1 IEC 61156-5 Cat 7 ISO/IEC 11801 Class F

Dimensions

Cable Length	500 m 1,640.42 ft
Cable Length Tolerance	±5%
Diameter Over Jacket, nominal	7.399 mm 0.291 in

Jacket Thickness	0.635 mm 0.025 in
Conductor Gauge, singles	23 AWG

Cross Section Drawing



Electrical Specifications

dc Resistance Unbalance, maximum	2 %
dc Resistance, maximum	7.61 ohms/100 m 2.32 ohms/100 ft
Dielectric Strength, minimum	2500 Vdc
Mutual Capacitance at Frequency	4.2 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	80 %
Operating Frequency, maximum	600 MHz
Operating Voltage, maximum	80 V
Segregation Class	d

Electrical Cable Performance

CS	CommScope		
STD	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above		
TYP	Typical Electrical Performance		
IL	Insertion Loss (dB/100m)	NEXT	Near End Crosstalk (dB/100m)
ACR	Attenuation to Crosstalk Ratio (dB/100m)	PSNEXT	Power Sum Near End Crosstalk (db/100m)
PSACR	Power Sum Attenuation to Crosstalk Ratio (dB/100m)	ACRF	Attenuation to Crosstalk Ratio - Far End (dB/100m)
PSACRF	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)	RL	Return Loss (dB)
TCL	Transverse Conversion Loss (dB/100m)	ELTCTL	Equal Level Transverse Conversion Transfer Loss (dB/100m)

Freq. MHz	IL	NEXT	PSNEXT	ACRF	PSACRF	RL
	STD	STD	STD	STD	STD	STD
1	2	78	75	78	75	20
4	3.7	78	75	78	75	23
8	5.2	78	75	77.2	74.2	24.5
10	5.9	78	75	75.3	72.3	25
16	7.4	78	75	71.2	68.2	25
20	8.3	78	75	69.3	66.3	25
25	9.3	78	75	67.3	64.3	24.3
31.25	10.4	78	75	65.4	62.4	23.6
62.5	14.9	75.5	72.5	59.4	56.4	21.5
100	19	72.4	69.4	55.3	52.3	20.1
155	24	69.5	66.5	51.5	48.5	18.8
200	27.5	67.9	64.9	49.3	46.3	18
250	31	66.4	63.4	47.3	44.3	17.3
300	34.2	65.2	62.2	45.8	42.8	17.3
350	37.2	64.2	61.2	44.4	41.4	17.3
400	40	63.4	60.4	43.3	40.3	17.3
500	45.3	61.9	58.9	41.3	38.3	17.3
550	47.7	61.3	58.3	40.5	37.5	17.3
600	50.1	60.7	57.7	39.7	36.7	17.3
650	52.4	60.2	57.2	39	36	17.3

Material Specifications

Conductor Material	Bare copper
Insulation Material	Polyolefin
Jacket Material	Low Smoke Zero Halogen (LSZH)
Separator Material	Polyolefin
Shield (Braid) Material	Tinned copper
Shield (Tape) Material	Polyester/Aluminum shield

Mechanical Specifications

Pulling Tension, maximum	11.34 kg 25 lb
--------------------------	------------------

Environmental Specifications

Installation temperature	0 °C to +50 °C (+32 °F to +122 °F)
Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Acid Gas Test Method	EN 50267-2-3
EN50575 CPR Cable EuroClass Fire Performance	Cca
EN50575 CPR Cable EuroClass Smoke Rating	s1
EN50575 CPR Cable EuroClass Droplets Rating	d1
EN50575 CPR Cable EuroClass Acidity Rating	a1
Environmental Space	Low Smoke Zero Halogen (LSZH)
Smoke Test Method	IEC 61034-2

Packaging and Weights

Cable weight	56.997 kg/km 38.3 lb/kft
Packaging Type	Reel

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

