

CS44Z1 Category 6A, F/UTP Cable, low smoke zero halogen, white jacket, 4 pair count, 1000 ft (305 m) length reel

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   China   India   Latin America
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Twisted pair cable


## General Specifications

<b>Product Number</b>	CS44Z1
<b>ANSI/TIA Category</b>	6A
<b>Cable Component Type</b>	Horizontal
<b>Cable Type</b>	F/UTP (shielded)
<b>Conductor Type, singles</b>	Solid
<b>Conductors, quantity</b>	8
<b>Drain Wire Type</b>	Solid
<b>Jacket Color</b>	White
<b>Note</b>	All electrical transmission tests include swept frequency measurements
<b>Pairs, quantity</b>	4
<b>Separator Type</b>	Isolator
<b>Transmission Standards</b>	ANSI/TIA-568.2-D   ISO/IEC 11801 Class EA

## Dimensions

<b>Cable Length</b>	304.8 m   1000 ft
<b>Diameter Over Insulated Conductor</b>	1.14 mm   0.045 in
<b>Diameter Over Jacket, nominal</b>	7.188 mm   0.283 in
<b>Conductor Gauge, singles</b>	23 AWG
<b>Drain Wire Gauge</b>	26 AWG

## Cross Section Drawing



## Electrical Specifications

<b>Characteristic Impedance</b>	100 ohm
<b>Characteristic Impedance Tolerance</b>	±15 ohm
<b>dc Resistance, maximum</b>	7.8 ohms/100 m   2.377 ohms/100 ft
<b>Delay Skew, maximum</b>	45 ns
<b>Dielectric Strength, minimum</b>	1500 Vac   2500 Vdc
<b>Mutual Capacitance at Frequency</b>	5.6 nF/100 m @ 1 kHz
<b>Nominal Velocity of Propagation (NVP)</b>	69 %
<b>Operating Frequency, maximum</b>	500 MHz
<b>Operating Voltage, maximum</b>	80 V
<b>Propagation Delay, maximum</b>	536 ns/100m @500MHz
<b>Remote Powering</b>	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A
<b>Segregation Class</b>	c

## Electrical Cable Performance

<b>CS</b>	CommScope	<b>NEXT</b>	Near End Crosstalk (dB/100m)
<b>STD</b>	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above	<b>PSNEXT</b>	Power Sum Near End Crosstalk (db/100m)
<b>TYP</b>	Typical Electrical Performance	<b>ACRF</b>	Attenuation to Crosstalk Ratio - Far End (dB/100m)
<b>IL</b>	Insertion Loss (dB/100m)	<b>RL</b>	Return Loss (dB)
<b>ACR</b>	Attenuation to Crosstalk Ratio (dB/100m)	<b>ELTCTL</b>	Equal Level Transverse Conversion Transfer Loss (dB/100m)
<b>PSACR</b>	Power Sum Attenuation to Crosstalk Ratio (dB/100m)		
<b>PSACRF</b>	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)		
<b>TCL</b>	Transverse Conversion Loss (dB/100m)		

Freq. MHz	IL	NEXT	ACR	PSNEXT	PSACR	ACRF	PSACRF	RL
	STD	STD	STD	STD	STD	STD	STD	STD
1	2.1	75.3	73.2	72.3	70.2	68	65	20
4	3.8	66.3	62.5	63.3	59.5	56	53	23
8	5.3	61.8	56.4	58.8	53.4	49.9	46.9	24.5
10	5.9	60.3	54.4	57.3	51.4	48	45	25
16	7.5	57.2	49.8	54.2	46.8	43.9	40.9	25
20	8.4	55.8	47.4	52.8	44.4	42	39	25
25	9.4	54.3	45	51.3	42	40	37	24.3
31.25	10.5	52.9	42.4	49.9	39.4	38.1	35.1	23.6
62.5	15	48.4	33.4	45.4	30.4	32.1	29.1	21.5
100	19.1	45.3	26.2	42.3	23.2	28	25	20.1
155	24.1	42.4	18.4	39.4	15.4	24.2	21.2	18.8
200	27.6	40.8	13.2	37.8	10.2	22	19	18
250	31.1	39.3	8.3	36.3	5.3	20	17	17.3
300	34.3	38.1	3.9	35.1	0.9	18.5	15.5	16.8
350	37.2	37.1	-0.1	34.1	-3.1	17.1	14.1	16.3
400	40.1	36.3	-3.8	33.3	-6.8	16	13	15.9
500	45.3	34.8	-10.4	31.8	-13.4	14	11	15.2

## Material Specifications

<b>Conductor Material</b>	Bare copper
<b>Insulation Material</b>	Polyolefin
<b>Jacket Material</b>	Low Smoke Zero Halogen (LSZH)
<b>Shield (Tape) Material</b>	Aluminum/Polyester

## Mechanical Specifications

<b>Minimum Bend Radius Note</b>	8 times the outer cable diameter
<b>Pulling Tension, maximum</b>	11.34 kg   25 lb

## Environmental Specifications

<b>Installation temperature</b>	0 °C to +60 °C (+32 °F to +140 °F)
<b>Operating Temperature</b>	-20 °C to +75 °C (-4 °F to +167 °F)
<b>Acid Gas Test Method</b>	IEC 60754-2
<b>EN50575 CPR Cable EuroClass Fire Performance</b>	No Rating
<b>Environmental Space</b>	Low Smoke Zero Halogen (LSZH)
<b>Temperature Rating, UL</b>	75 °C   167 °F
<b>Flame Test Method</b>	IEC 60332-1
<b>Smoke Test Method</b>	IEC 61034-2

## Packaging and Weights

<b>Packaging Type</b>	Reel
-----------------------	------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

