


884035958/16 | CS44ZC WHT C6A 4/23 F/FTP RL 500M



CS44ZC Category 6A F/FTP Cable, low smoke zero halogen, white jacket, 4 pair count, 1640 ft (500 m) length, reel

OBSOLETE

This product was discontinued on: October 1, 2024

Replaced By:

884048458/16 CS44ZB Category 6A F/FTP Cable, low smoke zero halogen, white jacket, 4 pair count, 1640 ft (500 m) length, reel

Product Classification

Regional Availability	EMEA
Portfolio	NETCONNECT®
Product Type	Twisted pair cable

General Specifications


Product Number	CS44ZC
ANSI/TIA Category	6A
Cable Component Type	Horizontal
Cable Type	F/FTP (shielded)
Conductor Type, singles	Solid
Conductors, quantity	8
Jacket Color	White
Pairs, quantity	4
Transmission Standards	ANSI/TIA-568.2-D IEC 61156-5 Grade 2 IEC 61156-5 Type Ib ISO /IEC 11801 Class EA

Dimensions

Cable Length	500 m 1,640.42 ft
Cable Length Tolerance	±5%
Diameter Over Insulated Conductor	1.168 mm 0.046 in
Diameter Over Jacket, nominal	7.01 mm 0.276 in

Jacket Thickness	0.635 mm 0.025 in
Conductor Gauge, singles	23 AWG

Cross Section Drawing



Electrical Specifications

Coupling Attenuation	Type II
dc Resistance Unbalance, maximum	2 %
dc Resistance, maximum	7.61 ohms/100 m 2.32 ohms/100 ft
Dielectric Strength, minimum	2500 Vdc
Mutual Capacitance at Frequency	4.2 nF/100 m @ 1 kHz
Nominal Velocity of Propagation (NVP)	80 %
Operating Frequency, maximum	500 MHz
Operating Voltage, maximum	80 V
Remote Powering	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A
Segregation Class	d
Transfer Impedance	Grade 2

Electrical Cable Performance

CS	CommScope		
STD	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above		
TYP	Typical Electrical Performance		
IL	Insertion Loss (dB/100m)	NEXT	Near End Crosstalk (dB/100m)
ACR	Attenuation to Crosstalk Ratio (dB/100m)	PSNEXT	Power Sum Near End Crosstalk (db/100m)
PSACR	Power Sum Attenuation to Crosstalk Ratio (dB/100m)	ACRF	Attenuation to Crosstalk Ratio - Far End (dB/100m)
PSACRF	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)	RL	Return Loss (dB)
TCL	Transverse Conversion Loss (dB/100m)	ELTCTL	Equal Level Transverse Conversion Transfer Loss (dB/100m)

Freq. MHz	IL		NEXT		ACR		PSNEXT		PSACR		ACRF		PSACRF		RL		TCL		ELTCTL	
	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP
1	2.1	1.9	75.3	98.4	73.2	96.5	72.3	96.6	70.2	94.6	68	98.9	65	96.6	20	29	40	61.9	35	61.7
4	3.8	3.5	66.3	99.9	62.5	96.3	63.3	97.8	59.5	94.2	56	98.2	53	95.6	23	30.1	34	55.9	23	56.1
8	5.3	4.9	61.8	96.1	56.4	91.2	58.8	93.8	53.4	88.9	49.9	94.6	46.9	92.1	24.5	34.9	31	57.2	16.9	56.6
10	5.9	5.5	60.3	95.5	54.4	90.1	57.3	93.3	51.4	87.9	48	92.2	45	89.8	25	34.8	30	54.1	15	53.7
16	7.5	6.9	57.2	93	49.8	86	54.2	90.7	46.8	83.8	43.9	89.1	40.9	86.5	25	35.9	28	51.6	10.9	51.9
20	8.4	7.8	55.8	90	47.4	82.2	52.8	87.6	44.4	79.8	42	88.3	39	85.8	25	35.8	27	52.8	9	52
25	9.4	8.8	54.3	88.5	45	79.7	51.3	86.1	42	77.3	40	87.1	37	84.7	24.3	34.6	26	51.6	7	51.3
31.25	10.5	9.9	52.9	88.7	42.4	78.8	49.9	86.2	39.4	76.3	38.1	85.5	35.1	83.1	23.6	32.7	25.1	50.7		
62.5	15	14.1	48.4	86.1	33.4	72	45.4	83.9	30.4	69.7	32.1	79.7	29.1	77.4	21.5	30	22	46.5		
100	19.1	17.9	45.3	79.8	26.2	61.9	42.3	78.4	23.2	60.5	28	70.9	25	68.9	20.1	27	20	43.8		
155	24.1	22.4	42.4	82.1	18.4	59.8	39.4	79.9	15.4	57.6	24.2	69.1	21.2	66.9	18.8	23.4	18.1	40.9		
200	27.6	25.5	40.8	79.6	13.2	54.1	37.8	77.5	10.2	52	22	62	19	59.9	18	21	17	39.1		
250	31.1	28.6	39.3	76.1	8.3	47.5	36.3	74.3	5.3	45.7	20	63.9	17	61.4	17.3	19	16	36.5		
300	34.3	31.4	38.1	70.9	3.9	39.5	35.1	69.6	0.9	38.2	18.5	62.2	15.5	59.9	16.8	18				35.9
350	37.2	34.1	37.1	73.4		39.4	34.1	72		37.9	17.1	55.6	14.1	53.5	16.3	16.9		35		
400	40.1	36.4	36.3	73.2		36.8	33.3	71.4		35	16	54.4	13	52.3	15.9	16		34		
500	45.3	41.1	34.8	68.8		27.7	31.8	67.1		26.1	14	42.9	11	40.7	15.2	15.2		33.1		

Material Specifications

Conductor Material	Bare copper
Insulation Material	Polyolefin
Jacket Material	Low Smoke Zero Halogen (LSZH)
Shield (Tape) Material	Polyester/Aluminum shield

Mechanical Specifications

Pulling Tension, maximum	11.34 kg 25 lb
--------------------------	------------------

Environmental Specifications

Installation temperature	0 °C to +50 °C (+32 °F to +122 °F)
--------------------------	------------------------------------

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Acid Gas Test Method	EN 50267-2-3
EN50575 CPR Cable EuroClass Fire Performance	Cca
EN50575 CPR Cable EuroClass Smoke Rating	s1a
EN50575 CPR Cable EuroClass Droplets Rating	d1
EN50575 CPR Cable EuroClass Acidity Rating	a1
Environmental Space	Low Smoke Zero Halogen (LSZH)
Smoke Test Method	IEC 61034-2

Packaging and Weights

Cable weight	48.499 kg/km 32.59 lb/kft
Packaging Type	Reel

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

