


# UN884024104/10 | CS44R RED C6A 4/23 F/UTP RL 1KFT

---

CS44R ETL Verified Category 6A F/UTP Cable, non-plenum, red jacket, 4 pair count, 1000 ft (305 m) length reel



## Product Classification

<b>Regional Availability</b>	North America
<b>Portfolio</b>	Uniprise®
<b>Product Type</b>	Twisted pair cable


## General Specifications

<b>Product Number</b>	CS44R
<b>ANSI/TIA Category</b>	6A
<b>Cable Component Type</b>	Horizontal
<b>Cable Type</b>	F/UTP (shielded)
<b>Conductor Type, singles</b>	Solid
<b>Conductors, quantity</b>	8
<b>Drain Wire Type</b>	Solid
<b>Jacket Color</b>	Red
<b>Pairs, quantity</b>	4
<b>Separator Type</b>	Isolator
<b>Transmission Standards</b>	ANSI/TIA-568.2-D

## Dimensions

<b>Cable Length</b>	304.8 m   1000 ft
<b>Diameter Over Jacket, nominal</b>	7.518 mm   0.296 in
<b>Jacket Thickness</b>	0.508 mm   0.02 in
<b>Conductor Gauge, singles</b>	23 AWG
<b>Drain Wire Gauge</b>	26 AWG

## Cross Section Drawing



## Electrical Specifications

<b>dc Resistance Unbalance, maximum</b>	4 %
<b>dc Resistance, maximum</b>	8 ohms/100 m   2.438 ohms/100 ft
<b>Delay Skew, maximum</b>	45 ns
<b>Dielectric Strength, minimum</b>	1500 Vac   2500 Vdc
<b>Mutual Capacitance at Frequency</b>	5.6 nF/100 m @ 1 kHz
<b>Nominal Velocity of Propagation (NVP)</b>	68 %
<b>Operating Frequency, maximum</b>	500 MHz
<b>Operating Voltage, maximum</b>	80 V
<b>Remote Powering</b>	Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A
<b>Safety Voltage Rating</b>	300 V

## Electrical Cable Performance

<b>CS</b>	CommScope	<b>NEXT</b>	Near End Crosstalk (dB/100m)
<b>STD</b>	Refers to the standard value listed under Transmission Standards in the Electrical Specifications above	<b>PSNEXT</b>	Power Sum Near End Crosstalk (db/100m)
<b>TYP</b>	Typical Electrical Performance	<b>ACRF</b>	Attenuation to Crosstalk Ratio - Far End (dB/100m)
<b>IL</b>	Insertion Loss (dB/100m)	<b>RL</b>	Return Loss (dB)
<b>ACR</b>	Attenuation to Crosstalk Ratio (dB/100m)	<b>ELTCTL</b>	Equal Level Transverse Conversion Transfer Loss (dB/100m)
<b>PSACR</b>	Power Sum Attenuation to Crosstalk Ratio (dB/100m)		
<b>PSACRF</b>	Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m)		
<b>TCL</b>	Transverse Conversion Loss (dB/100m)		

Freq. MHz	IL		NEXT		ACR		PSNEXT		PSACR		ACRF		PSACRF		RL	
	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP	STD	TYP
1	2.1	1.7	74.3	89	72.2	87.2	72.3	86.6	70.2	84.9	67.8	89.2	64.8	86.9	20	30.9
4	3.8	3.4	65.3	83.6	61.5	80.2	63.3	81.5	59.5	78.2	55.8	82.1	52.8	80	23	33.5
8	5.3	4.8	60.8	76.6	55.4	71.8	58.8	74.8	53.4	70	49.7	75.2	46.7	73.4	24.5	35
10	5.9	5.4	59.3	75.7	53.4	70.4	57.3	73.9	51.4	68.5	47.8	72.8	44.8	71.1	25	36
16	7.5	6.8	56.2	73.4	48.8	66.6	54.2	71.4	46.8	64.6	43.7	69.4	40.7	67.6	25	37.2
20	8.4	7.6	54.8	71.9	46.4	64.3	52.8	69.8	44.4	62.2	41.8	67.5	38.8	65.9	25	36.2
25	9.4	8.5	53.3	70.1	44	61.6	51.3	68.1	42	59.6	39.8	65.7	36.8	64	24.3	34.9
31.25	10.5	9.5	51.9	68.5	41.4	59	49.9	66.4	39.4	56.9	37.9	63.5	34.9	61.8	23.6	34.6
62.5	15	13.5	47.4	64.6	32.4	51.1	45.4	62.5	30.4	49	31.9	57.8	28.9	56.1	21.5	31.7
100	19.1	17.2	44.3	61.1	25.2	43.9	42.3	59.2	23.2	42	27.8	54.8	24.8	52.8	20.1	27.8
155	24.1	21.5	41.4	58.1	17.4	36.6	39.4	56	15.4	34.5	24	49.8	21	47.9	18.8	24.5
200	27.6	24.5	39.8	55.3	12.2	30.8	37.8	53.3	10.2	28.8	21.8	47.8	18.8	45.9	18	23.3
250	31.1	27.5	38.3	52.7	7.3	25.2	36.3	50.8	5.3	23.3	19.8	45.6	16.8	43.7	17.3	20.9
300	34.3	30.2	37.1	50.6	2.9	20.3	35.1	48.8	0.9	18.6	18.3	44.5	15.3	42.3	16.8	20.2
350	37.2	32.8	36.1	48.5	-1.1	15.8	34.1	46.9	-3.1	14.1	16.9	42.6	13.9	40.4	16.3	19.4
400	40.1	35.1	35.3	48.3	-4.8	13.1	33.3	46.5	-6.8	11.4	15.8	40.1	12.8	38	15.9	18.4
500	45.3	39.6	33.8	47.4	-11.4	7.8	31.8	45.3	-13.4	5.8	13.8	38.1	10.8	35.9	15.2	17.7
550		41.7		46.1		4.4		44.1		2.4		36.5		34.1		16.9

## Material Specifications

<b>Conductor Material</b>	Bare copper
<b>Drain Wire Material</b>	Tinned copper
<b>Insulation Material</b>	Polyolefin
<b>Jacket Material</b>	PVC
<b>Separator Material</b>	Polyolefin

## Mechanical Specifications

**Pulling Tension, maximum** 11.34 kg | 25 lb

## Environmental Specifications

# UN884024104/10 | CS44R RED C6A 4/23 F/UTP RL 1KFT

---

<b>Installation temperature</b>	0 °C to +60 °C (+32 °F to +140 °F)
<b>Operating Temperature</b>	-20 °C to +60 °C (-4 °F to +140 °F)
<b>Environmental Space</b>	Non-plenum
<b>Flame Test Method</b>	CMR   NEC Article 800   UL 1666   UL 444

## Packaging and Weights

<b>Cable weight</b>	57.518 kg/km   38.65 lb/kft
<b>Packaging Type</b>	Reel

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system