

FFV4-65B-R6-V3



12-port sector antenna, 4x 617-894 and 8x 1695-2690 MHz, 65° HPBW, 6x RET

- Similar to FFV4-65B-R6-V2, except 0-10 tilt for mid band arrays

General Specifications

Antenna Type	Sector
Band	Multiband
Color	Light Gray (RAL 7035)
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Performance Note	Outdoor usage
Radome Material	Fiberglass, UV resistant
Reflector Material	Aluminum
RF Connector Interface	4.3-10 Female
RF Connector Location	Bottom
RF Connector Quantity, mid band	8
RF Connector Quantity, low band	4
RF Connector Quantity, total	12

Remote Electrical Tilt (RET) Information

RET Hardware	CommRET v2
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	1 female 1 male
Input Voltage	10-30 Vdc
Internal RET	Low band (2) Mid band (4)
Power Consumption, active state, maximum	8 W
Power Consumption, idle state, maximum	1 W
Protocol	3GPP/AISG 2.0 (Single RET)


Dimensions

Width	498 mm 19.606 in
--------------	--------------------

FFV4-65B-R6-V3

Depth	197 mm 7.756 in
Length	2000 mm 78.74 in
Net Weight, without mounting kit	38.6 kg 85.098 lb

Array Layout



Array ID	Frequency (MHz)	RF Connector	RET (SRET)	AISG RET UID
R1	617-894	1 - 2	1	CPxxxxxxxxxxxxxxxxR1
R2	617-894	3 - 4	2	CPxxxxxxxxxxxxxxxxR2
Y1	1695-2690	5 - 6	3	CPxxxxxxxxxxxxxxxxY1
Y2	1695-2690	7 - 8	4	CPxxxxxxxxxxxxxxxxY2
Y3	1695-2690	9 - 10	5	CPxxxxxxxxxxxxxxxxY3
Y4	1695-2690	11 - 12	6	CPxxxxxxxxxxxxxxxxY4

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration



Electrical Specifications

Impedance	50 ohm
Operating Frequency Band	1695 – 2690 MHz 617 – 894 MHz

FFV4-65B-R6-V3

Polarization	±45°
Total Input Power, maximum	1,400 W @ 50 °C

Electrical Specifications

Frequency Band, MHz	617-698	698-894	1695-1880	1850-1990	1920-2200	2300-2500	2500-2690
Gain, dBi	14.7	15.3	16.3	17	17.2	17.5	17.9
Beamwidth, Horizontal, degrees	64	57	65	63	60	58	56
Beamwidth, Vertical, degrees	12.1	10.5	6.5	6.2	5.8	5.3	5
Beam Tilt, degrees	2-14	2-14	0-10	0-10	0-10	0-10	0-10
USLS (First Lobe), dB	15	17	15	16	17	19	18
Front-to-Back Ratio at 180°, dB	29	31	33	34	33	31	30
Isolation, Cross Polarization, dB	25	25	25	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25	25	25	25
VSWR Return loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150	-150
Input Power per Port at 50°C, maximum, watts	250	250	200	200	200	200	200

Electrical Specifications, BASTA

Frequency Band, MHz	617-698	698-894	1695-1880	1850-1990	1920-2200	2300-2500	2500-2690
Gain by all Beam Tilts, average, dBi	14.4	14.9	15.8	16.6	16.9	17.1	17.3
Gain by all Beam Tilts Tolerance, dB	±0.5	±0.5	±0.8	±0.5	±0.5	±0.6	±0.7
Beamwidth, Horizontal Tolerance, degrees	±4.5	±5.4	±7.1	±6	±6.6	±5.4	±6
Beamwidth, Vertical Tolerance, degrees	±0.7	±1	±0.5	±0.3	±0.4	±0.3	±0.4
USLS, beampeak to 20° above beampeak, dB	15	16	14	15	15	15	14
Front-to-Back Total Power at 180° ± 30°, dB	22	22	25	28	27	26	23
CPR at Boresight, dB	17	16	17	19	19	20	22
CPR at Sector, dB	10	7	8	8	8	5	4

Mechanical Specifications

FFV4-65B-R6-V3

Wind Loading @ Velocity, frontal	688.0 N @ 150 km/h (154.7 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	210.0 N @ 150 km/h (47.2 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	826.0 N @ 150 km/h (185.7 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	474.0 N @ 150 km/h (106.6 lbf @ 150 km/h)
Wind Speed, maximum	241 km/h (150 mph)

Packaging and Weights

Width, packed	565 mm 22.244 in
Depth, packed	309 mm 12.165 in
Length, packed	2187 mm 86.102 in
Weight, gross	53 kg 116.845 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



Included Products

BSAMNT-4	-	Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.
----------	---	--

* Footnotes

Performance Note	Severe environmental conditions may degrade optimum performance
-------------------------	---