

# 6-port sector antenna, 2x 694–960 and 4x 1695–2690 MHz, 65° HPBW, 3x RET with manual override and SBT on every RF port

- Each port has an integrated bias tee, and each band has its own smart switch that automatically selects between bias tee or AISG inputs according to a predetermined priority table
- All Internal RET actuators are in SRET configuration, with dedicated AISG ports for each band

### General Specifications

Antenna Type Sector

Band Multiband

**Grounding Type** RF connector body grounded to reflector and mounting bracket

Performance Note Outdoor usage | Wind loading figures are validated by wind tunnel

measurements described in white paper WP-112534-EN

Radome MaterialFiberglass, UV resistantRadiator MaterialLow loss circuit board

Reflector Material Aluminum

**RF Connector Interface** 7-16 DIN Female

**RF Connector Location** Bottom

RF Connector Quantity, high band 4
RF Connector Quantity, mid band 0
RF Connector Quantity, low band 2
RF Connector Quantity, total 6

## Remote Electrical Tilt (RET) Information

**RET Interface** 8-pin DIN Female | 8-pin DIN Male

**RET Interface, quantity** 1 female | 3 male

Input Voltage 10-30 Vdc

Internal Bias Tee Port 1 | Port 2 | Port 3 | Port 4 | Port 5 | Port 6

Internal RET High band (2) | Low band (1)

Power Consumption, idle state, maximum 2 W
Power Consumption, normal conditions, maximum 13 W

Protocol 3GPP/AISG 2.0 (Single RET)



#### **Dimensions**

Width 350 mm | 13.78 in **Depth** 208 mm | 8.189 in Length 1584 mm | 62.362 in

Net Weight, without mounting kit 24.7 kg | 54.454 lb

## Array Layout



Array	Freq (MHz)	Conns	RET (SRET)	AISG RET UID
R1	694-960	1-2	1	ARxxxxxxxxxxxxxxxx1
Y1	1695-2690	3-4	2	ARxxxxxxxxxxxxxxxx
Y2	1695-2690	5-6	3	ARxxxxxxxxxxxxx3

Right Bottom

(Sizes of colored boxes are not true depictions of array sizes)

## Port Configuration





## **Electrical Specifications**

**Impedance** 50 ohm

**Operating Frequency Band** 1695 – 2690 MHz | 694 – 960 MHz

Polarization ±45°

**Total Input Power, maximum** 650 W @ 50 °C

## **Electrical Specifications**

ı						
Frequency Band, MHz	694-790	790-890	890-960	1695-1920	1920-2180	2300-2690
Gain, dBi	14.3	14.9	15.2	17.2	17.8	18.4
Beamwidth, Horizontal, degrees	69	67	66	62	62	64
Beamwidth, Vertical, degrees	16.5	14.6	13.6	7.5	6.7	5.5
Beam Tilt, degrees	2-12	2-12	2-12	0-10	0-10	0-10
USLS (First Lobe), dB	15	18	21	18	20	19
Front-to-Back Ratio at 180°, dB	30	32	33	36	37	38
Isolation, Cross Polarization, dB	27	27	27	28	28	28
Isolation, Inter-band, dB	28	28	28	28	28	28
VSWR   Return loss, dB	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0	1.5   14.0

Page 4 of 5



PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150
Input Power per Port at 50°C,	150	150	150	150	150	100
maximum, watts						

### Mechanical Specifications

Wind Loading @ Velocity, frontal	255.0 N @ 150 km/h (57.3 lbf @ 150 km/h)
Wind Loading @ Velocity, lateral	214.0 N @ 150 km/h (48.1 lbf @ 150 km/h)
Wind Loading @ Velocity, maximum	540.0 N @ 150 km/h (121.4 lbf @ 150 km/h)
Wind Loading @ Velocity, rear	270.0 N @ 150 km/h (60.7 lbf @ 150 km/h)

Wind Speed, maximum 241 km/h (150 mph)

### Packaging and Weights

 Width, packed
 420 mm | 16.535 in

 Depth, packed
 310 mm | 12.205 in

 Length, packed
 1760 mm | 69.291 in

 Weight, gross
 41.4 kg | 91.271 lb

### Regulatory Compliance/Certifications

#### Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



#### Included Products

T-041-GL-E – Adjustable Tilt Pipe Mounting Kit for 2.0"-4.5" (60-115mm) OD round members for panel antennas. Includes 2 clamp sets.

#### \* Footnotes

**Performance Note** Severe environmental conditions may degrade optimum performance

