

Fiber OSP cable, Zero Water Peak® Blown Micro Single Jacket All-Dielectric Stranded Loose Tube, Singlemode G.657.A1, 216 fiber, Gel-filled, 200um Fiber Arid-Core™ Construction, Meters jacket marking, Black jacket color

## Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	B-LN


## General Specifications

Cable Type	Stranded loose tube
Construction Type	Non-armored
Subunit Type	Gel-filled
Filler, quantity	0
Jacket Color	Black
Jacket Marking	Meters
Jacket Marking Method	Laser
Jacket Marking Text	COMMScope OPTICAL CABLE G657A1 SM 216F [SERIAL NUMBER] MM/YYYY [METERS] M
Subunit, quantity	9
Fibers per Subunit, quantity	24
Total Fiber Count	216

## Dimensions

Buffer Tube/Subunit Diameter	1.7 mm   0.067 in
Diameter Over Jacket	7.8 mm   0.307 in

## Representative Image



## Material Specifications

Jacket Material

High density polyethylene (HDPE)

## Mechanical Specifications

Minimum Bend Radius, loaded	117 mm   4.606 in
Minimum Bend Radius, unloaded	78 mm   3.071 in
Tensile Load, long term, maximum	335 N   75.311 lbf
Tensile Load, short term, maximum	1000 N   224.809 lbf
Compression	10 N/mm   57.101 lb/in
Compression Test Method	FOTP-41   IEC 60794-1 E3
Flex	25 cycles
Flex Test Method	FOTP-104   IEC 60794-1 E6
Impact	0.3 N-m   2.655 in lb
Impact Test Method	FOTP-25   IEC 60794-1 E4
Strain	See long and short term tensile loads
Strain Test Method	FOTP-33   IEC 60794-1 E1
Twist	10 cycles
Twist Test Method	FOTP-85   IEC 60794-1 E7
Vertical Rise, maximum	769 m   2,522.966 ft

## Optical Specifications

Fiber Type

G.657.A1, TeraSPEED®

## Environmental Specifications

810009726/DB | B-216-LN-8F-M24NS/17T 200

---

Installation temperature	-30 °C to +70 °C (-22 °F to +158 °F)
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Cable Qualification Standards	IEC 60794-5-10
Environmental Space	Air-blown, microduct
Jacket UV Resistance	UV stabilized
Water Penetration	24 h
Water Penetration Test Method	FOTP-82   IEC 60794-1 F5

### Environmental Test Specifications

Cable Freeze	-2 °C   28.4 °F
Cable Freeze Test Method	FOTP-98   IEC 60794-1 F15
Drip	70 °C   158 °F
Drip Test Method	FOTP-81   IEC 60794-1 E14
Heat Age	-40 °C to +85 °C (-40 °F to +185 °F)
Heat Age Test Method	IEC 60794-1 F9
Low High Bend	-30 °C to +60 °C (-22 °F to +140 °F)
Low High Bend Test Method	FOTP-37   IEC 60794-1 E11
Temperature Cycle	-40 °C to +70 °C (-40 °F to +158 °F)
Temperature Cycle Test Method	FOTP-3   IEC 60794-1 F1

### Packaging and Weights

Cable weight	52.9 kg/km   35.547 lb/kft
--------------	----------------------------

### Included Products

CS-8F-200UM-LT	–	200 Micron Low Macrobending, Zero Water Peak, Dispersion-Unshifted Singlemode Fiber
----------------	---	---

### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable