

Fiber OSP cable, LightScope® ZWP Blown Micro Single Jacket, 72 fiber, All-Dielectric Stranded Loose Tube Arid-Core™ Construction, Gel-filled, Singlemode G.652.D and G.657.Al, Feet jacket marking, Black jacket color

 *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North

America

Portfolio CommScope®

Product Type Fiber OSP cable

Product Series B-LN

Government RequirementsBuild America Buy America (BABA) compliant*

General Specifications

Cable Type Stranded loose tube

Construction Type Non-armored

Subunit Type Gel-filled

Filler, quantity 0

Jacket ColorBlackJacket MarkingFeetJacket Marking MethodLaser

Jacket Marking Text COMMSCOPE OPTICAL CABLE OS2 SM 72F (SERIAL NUMBER) MM/YYYY

XXXXXXXFT

Location of ManufacturingClaremont, North Carolina

Subunit, quantity 6
Fibers per Subunit, quantity 12

Total Fiber Count 72

Dimensions




Buffer Tube/Subunit Diameter

Diameter Over Jacket

1.45 mm | 0.057 in 5.3 mm | 0.209 in

Representative Image



Material Specifications

Jacket Material High density polyethylene (HDPE)

Mechanical Specifications

Minimum Bend Radius, loaded 226.1 mm | 8.902 in

Minimum Bend Radius, unloaded 68 mm | 2.677 in

Tensile Load, long term, maximum 180 N | 40.466 lbf

Tensile Load, short term, maximum 600 N | 134.885 lbf

Compression 10 N/mm | 57.101 lb/in

Compression Test Method IEC 60794-1-21 E3

Flex 25 cycles

Flex Test Method IEC 60794-1 E6

Impact 0.3 N-m | 2.655 in lb

Impact Test Method IEC 60794-1-21 E4

Strain See long and short term tensile loads

Strain Test Method IEC 60794-1-21 E1

Twist 10 cycles

COMMSCOPE®

 Twist Test Method
 IEC 60794-1-21 E7

 Vertical Rise, maximum
 721 m | 2,365.486 ft

Optical Specifications

Fiber Type G.652.D | G.652.D and G.657.A1

Environmental Specifications

Installation temperature-30 °C to +70 °C (-22 °F to +158 °F)Operating Temperature-30 °C to +70 °C (-22 °F to +158 °F)Storage Temperature-30 °C to +75 °C (-22 °F to +167 °F)

Cable Qualification StandardsIEC 60794-5-10

Environmental Space Air-blown, microduct

Jacket UV Resistance UV stabilized

Water Penetration 24 h

Water Penetration Test Method IEC 60794-1 F4

Environmental Test Specifications

 Cable Freeze
 -2 °C | 28.4 °F

 Cable Freeze Test Method
 IEC 60794-1 F15

 Drip
 70 °C | 158 °F

 Drip Test Method
 IEC 60794-1-21 E14

Heat Age -30 °C to +85 °C (-22 °F to +185 °F)

Heat Age Test Method IEC 60794-1-22 F9

Low High Bend $-30 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Low High Bend Test Method IEC 60794-1-21 E11

Temperature Cycle $-30 \,^{\circ}\text{C} \text{ to } +70 \,^{\circ}\text{C} \, (-22 \,^{\circ}\text{F to } +158 \,^{\circ}\text{F})$

Temperature Cycle Test Method IEC 60794-1-22 F1

Packaging and Weights

Cable weight 24 kg/km | 16.127 lb/kft

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

COMMSCOPE®

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Included Products

CS-8W-250-B-LN - TeraSPEED® G652D/G657A1 Singlemode Fiber

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable

