

# Installation Instructions

## Connector Attachment

Bulletin 7605304 Page 1 of 1

Revision B

For Braided Cable CNT-300, 5D-FB, WBC-300  
N Male, Straight, Captivated pin,  
Clamp-type Body: 300PNM-C-NC



300PNM-C-NC

**1** Remove 6.5 mm (0.256") of Jacket only, exposing braided wire.

**2** Comb the braided wires to straight.

**3** Fold braid around jacket out as shown.

**4** Remove 5.0 mm (0.197") of foam. Remove all foam/glue residue from the center conductor.

**5** Make the braid small and sharp at the front; Slide part B and Screw part A onto cable without damaging the braid.

**6** Fold braid around part A and comb braid as shown, the braid should be straight and equally spaced after comb.

**7** Cut off the redundant braid as shown.

**8** Chamfer the center conductor at a 45° angle.

**9** The cable center conductor must be straight and aligned with the connector inner contact. Insert the cable into the connector body until stopped; the center conductor must be inserted into the connector inner contact fingers. Tighten the connection to the torque value of 60-80 lb-in (6.8-9.0 Nm).  
Note: Do not turn connector body, turn clamp nut attachment.

	表一 有毒有害物质或元素名称及含量标识格式					
	有毒有害物质或元素					
部件名称 (Part Name)	铅 (Pb)	汞 (Hg)	镉 (Cd)	六价铬 (Cr6+)	多溴联苯 (PBB)	多溴二苯醚 (PBDE)
连接器 (Connector)	X	O	O	O	O	O

O: 表示有毒有害物质在该部件所有的均质材料中的含量均在SJ/T 11363-2006规定的限量要求以下。  
X: 表示该有毒有害物质至少在该部件的某一均质材料中的含量超出SJ/T 11363-2006规定的限量要求。



**Installation Training Available at Andrew Institute**

Notice: Andrew disclaims any liability or responsibility for the results of improper or unsafe installation, in section, maintenance, or removal practices

### Andrew Wireless Solutions

3 Westbrook Corporate Center, Suite 900, Westchester, Illinois U.S.A. 60154

+1 (779) 435-8579 Fax (U.S.A.): 1-800-349-5444

www.andrew.com

Copyright © 2010 by Andrew Corporation

### Customer Service, 24 hours

U.S.A., Canada, Mexico: 1-800-255-1479

U.K.: 0800 250055

Other Europe: +44 592 782 612

China: +86 512-6256-8805