

Ultra-Compact Twin Triplexer PCS/AWS/2496-2700MHz, NEX10 connectors

- BTS-to-feeder and feeder-to-antenna application
- Miniature NEX10™ series connector for superior PIM and compact size
- dc/AISG blocking on all ports
- Suitable for space limited applications like Metro Cell, Lamp Pole, Concealment Solution and Macro Site
- Ideal for small cell applications

#### **Product Classification**

Product Type Triplexer

#### General Specifications

ColorGrayCommon Port LabelCOMModularity2-Twin

MountingPole | WallMounting Pipe HardwareBand clamps (2)RF Connector InterfaceNEX10 Female

**RF Connector Interface Body Style**Long neck

#### **Dimensions**

 Height
 87 mm | 3.425 in

 Width
 259 mm | 10.197 in


 Depth
 46 mm | 1.811 in

 Ground Screw Diameter
 5 mm | 0.197 in

 Mounting Pipe Diameter Range
 42.6–122 mm

#### Outline Drawing





#### **Electrical Specifications**

**Impedance** 50 ohm

**License Band, Band Pass**AWS 1700 | AWS 2000 | DCS 1800 | IMT 2100 | IMT 2600 | PCS

1900 | TDD 2600

### Electrical Specifications, dc Power/Alarm

dc/AISG Pass-through Method No dc/AISG pass-through

**Lightning Surge Current** 5 kA

**Lightning Surge Current Waveform** 8/20 waveform

## **Electrical Specifications**

Sub-module	1   2	1   2	1   2
Branch	1	2	3
Port Designation	PCS	AWS	BRS


License Band PCS 1900, Band Pass AWS 1700, Band Pass TDD 2600, Band Pass AWS 2000, Band Pass IMT 2600, Band Pass

ANDREW® an Amphenol company

## Electrical Specifications, Band Pass

Frequency Range, MHz	1850-1995	1695-1780 2110-2200	2496-2700
Insertion Loss, maximum, dB	0.35	0.3	0.3
Total Group Delay, maximum, ns	15	15	8
Return Loss, typical, dB	20	20	20
Isolation, minimum, dB	35	35	35
Input Power, RMS, maximum, W	85	85	85
Input Power, PEP, maximum, W	1000	1000	1000
3rd Order PIM, typical, dBc	-155	-155	-155
3rd Order PIM Test Method	Two +43 dBm carriers	Two +43 dBm carriers	Two +43 dBm carriers

### Block Diagram



<sup>\*</sup> DC/AISG Block on all ports

#### **Environmental Specifications**

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +65 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +149 \,^{\circ}\text{F})$ 

**Relative Humidity** Up to 100%

**Corrosion Test Method** IEC 60068-2-11, 30 days

Ingress Protection Test Method IEC 60529:2001, IP67

Packaging and Weights

IncludedMounting hardwareMounting Hardware Weight0.16 kg | 0.353 lb

Volume 1.05 L



Weight, without mounting hardware

1.64 kg | 3.616 lb

