
# 884048304/10 | CS41CM BLU C6A 4/24 U/UTP RL 305M



CS41CM, ETL Verified Category 6A U/UTP Cable, non-plenum, blue jacket, 4 pair count, 1000 ft (305 m) length reel

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand

Portfolio NETCONNECT®

Product Type Twisted pair cable

General Specifications

**Product Number** CS41CM

ANSI/TIA Category 6A

Cable Component Type Horizontal

Cable Type U/UTP (unshielded)

Conductor Type, singles Solid
Conductors, quantity 8

Jacket Color Blue

Pairs, quantity 4

Separator Type Isolator

**Transmission Standards** ANSI/TIA-568.2-D | IEC 61156-5

**Dimensions** 

Cable Length304.8 m | 1000 ftDiameter Over Insulated Conductor1.08 mm | 0.043 inDiameter Over Jacket, nominal6.985 mm | 0.275 in


**Jacket Thickness** 0.508 mm | 0.02 in

Conductor Gauge, singles 24 AWG

Cross Section Drawing



# 884048304/10 | CS41CM BLU C6A 4/24 U/UTP RL 305M



### **Electrical Specifications**

dc Resistance Unbalance, maximum 4 %

**dc Resistance, maximum** 8 ohms/100 m | 2.438 ohms/100 ft

**Delay Skew, maximum** 45 ns

Dielectric Strength, minimum1500 Vac | 2500 VdcMutual Capacitance at Frequency5.6 nF/100 m @ 1 kHz

Nominal Velocity of Propagation (NVP) 67 %

Operating Frequency, maximum500 MHzOperating Voltage, maximum80 V

**Remote Powering** Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the

safe delivery of power over LAN cable when installed according to ISO/IEC 14763-2,

CENELEC EN 50174-1, CENELEC EN 50174-2 or TIA TSB-184-A

Safety Voltage Rating 300 V

# 884048304/10 | CS41CM BLU C6A 4/24 U/UTP RL 305M

#### Flectrical Cable Performance

**CS** CommScope

STD Refers to the standard value listed under Transmission Standards in the Electrical Specifications above

**TYP** Typical Electrical Performance

IL Insertion Loss (dB/100m) NEXT Near End Crosstalk (dB/100m)

 ACR
 Attenuation to Crosstalk Ratio (dB/100m)
 PSNEXT
 Power Sum Near End Crosstalk (db/100m)

 PSACR
 Power Sum Attenuation to Crosstalk Ratio (dB/100m)
 ACRF
 Attenuation to Crosstalk Ratio - Far End (dB/100m)

PSACRF Power Sum Attenuation to Crosstalk Ratio - Far End (dB/100m) RL Return Loss (dB)

TCL Transverse Conversion Loss (dB/100m) ELTCTL Equal Level Transverse Conversion Transfer Loss (dB/100m)

Freq. MHz	IL STD	NEXT STD	ACR STD	PSNEXT STD	PSACR STD	ACRF STD	PSACRF STD	RL STD
4	3.8	66.3	62.5	63.3	59.5	55.9	53	23
8	5.3	61.7	56.4	58.7	53.4	49.9	46.9	24.5
10	5.9	60.3	54.4	57.3	51.4	48	45	25
16	7.5	57.2	49.7	54.2	46.7	43.9	40.9	25
20	8.4	55.8	47.4	52.8	44.4	42	39	25
25	9.4	54.3	44.9	51.3	41.9	40	37	24.3
31.25	10.5	52.9	42.4	49.9	39.4	38.1	35.1	23.6
62.5	15	48.4	33.4	45.4	30.4	32.1	29.1	21.5
100	19.1	45.3	26.2	42.3	23.2	28	25	20.1
155	24.1	42.4	18.3	39.4	15.3	24.2	21.2	18.8
200	27.6	40.8	13.2	37.8	10.2	22	19	18
250	31.1	39.3	8.3	36.3	5.3	20	17	17.3
300	34.3	38.1	3.9	35.1	0.9	18.4	15.5	16.8
350	37.2	37.1	-0.1	34.1	-3.1	17.1	14.1	16.3
400	40.1	36.3	-3.8	33.3	-6.8	15.9	13	15.9
500	45.3	34.8	-10.5	31.8	-13.5	14	11	15.2

## Material Specifications

Conductor Material Bare copper

**Insulation Material** Polyolefin

Jacket Material PVC

Separator Material Polyolefin

**Tape Material** Poly/Aluminum/Poly

Mechanical Specifications

Pulling Tension, maximum 11.34 kg | 25 lb

**Environmental Specifications** 



# 884048304/10 | CS41CM BLU C6A 4/24 U/UTP RL 305M

Installation temperature  $0 \, ^{\circ}\text{C} \text{ to +60 } ^{\circ}\text{C} \text{ (+32 } ^{\circ}\text{F to +140 } ^{\circ}\text{F)}$ 

**Operating Temperature**  $-20 \,^{\circ}\text{C to } +60 \,^{\circ}\text{C (-4 °F to } +140 \,^{\circ}\text{F)}$ 

**Environmental Space** Non-plenum

Flame Test Method CM | NEC Article 800 | UL 1685 | UL 910

Packaging and Weights

**Cable weight** 44.273 kg/km | 29.75 lb/kft

Packaging Type Reel

### Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant

