


# P-024-MP-CM-F12RD/8W008/5L016



Fiber indoor cable, TeraSPEED® Plenum for MPO Trunks, 24 fiber with 12 fiber subunits, Multimode composite, Feet jacket marking, Red jacket color

## Product Classification

|                       |  |
|-----------------------|--|
| Regional Availability | Asia   Australia/New Zealand   Latin America   Middle East /Africa   North America |
| Portfolio             | CommScope®   |
| Product Type          | Fiber indoor cable   |
| Product Series        | P-MP   |

## General Specifications


|                              |                 |
|------------------------------|-----------------|
| Cable Type                   | MPO trunk cable |
| Construction Type            | Non-armored     |
| Subunit Type                 | Gel-free        |
| Jacket Color                 | Red             |
| Jacket Marking               | Feet            |
| Subunit, quantity            | 2               |
| Fibers per Subunit, quantity | 12              |
| Composite Fiber Count        | 8 + 16          |
| Total Fiber Count            | 24              |

## Dimensions

|                              |                   |
|------------------------------|-------------------|
| Height Over Jacket           | 3.9 mm   0.154 in |
| Width Over Jacket            | 6.9 mm   0.272 in |
| Buffer Tube/Subunit Diameter | 3 mm   0.118 in   |

## Representative Image

# P-024-MP-CM-F12RD/8W008/5L016



## Mechanical Specifications

|                                   |                                       |
|-----------------------------------|---------------------------------------|
| Minimum Bend Radius, loaded       | 58 mm   2.283 in                      |
| Minimum Bend Radius, unloaded     | 39 mm   1.535 in                      |
| Tensile Load, long term, maximum  | 200 N   44.962 lbf                    |
| Tensile Load, short term, maximum | 667 N   149.948 lbf                   |
| Compression                       | 10 N/mm   57.101 lb/in                |
| Compression Test Method           | FOTP-41   IEC 60794-1 E3              |
| Flex                              | 300 cycles                            |
| Flex Test Method                  | FOTP-104   IEC 60794-1 E6             |
| Impact                            | 0.74 N-m   6.55 in lb                 |
| Impact Test Method                | FOTP-25   IEC 60794-1 E4              |
| Strain                            | See long and short term tensile loads |
| Strain Test Method                | FOTP-33   IEC 60794-1 E1              |
| Twist                             | 10 cycles                             |
| Twist Test Method                 | FOTP-85   IEC 60794-1 E7              |
| Vertical Rise, maximum            | 500 m   1,640.42 ft                   |

## Optical Specifications

|            |  |
|------------|--|
| Fiber Type | Composite MM/SM   G.652.D and G.657.A1, TeraSPEED®   OM3, LazrSPEED® 300   OS2   OS2 |
|------------|--|

## Environmental Specifications

# P-024-MP-CM-F12RD/8W008/5L016

|                               |                                       |
|-------------------------------|---------------------------------------|
| Installation temperature      | 0 °C to +70 °C (+32 °F to +158 °F)    |
| Operating Temperature         | 0 °C to +70 °C (+32 °F to +158 °F)    |
| Storage Temperature           | -40 °C to +70 °C (-40 °F to +158 °F)  |
| Cable Qualification Standards | ANSI/ICEA S-83-596   Telcordia GR-409 |
| Environmental Space           | Plenum                                |
| Flame Test Listing            | NEC OFNP (ETL) and c(ETL)             |
| Flame Test Method             | NFPA 262                              |

## Environmental Test Specifications

|                               |                                    |
|-------------------------------|------------------------------------|
| Heat Age                      | 0 °C to +85 °C (+32 °F to +185 °F) |
| Heat Age Test Method          | IEC 60794-1 F9                     |
| Low High Bend                 | 0 °C to +70 °C (+32 °F to +158 °F) |
| Low High Bend Test Method     | FOTP-37   IEC 60794-1 E11          |
| Temperature Cycle             | 0 °C to +70 °C (+32 °F to +158 °F) |
| Temperature Cycle Test Method | FOTP-3   IEC 60794-1 F1            |

## Packaging and Weights

|              |                          |
|--------------|--------------------------|
| Cable weight | 29 kg/km   19.487 lb/kft |
|--------------|--------------------------|

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |

## Included Products

|          |   |
|----------|---|
| CS-5L-MP | – LazrSPEED® 300 OM3 Bend-Insensitive Multimode Fiber |
| CS-8W-MP | – TeraSPEED® OS2 Singlemode Fiber                     |

## \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable