# 760248413 | DM2-020-LS-MP024-LC



Fiber Optic LGX/1000 Style Multimode OM4 Distribution Module, 20LC to 1x20f MPO, Method A

# Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Fiber module
General Specifications	
Functionality	Breakout
Adapter Color	Aqua
Interface, front	LC/UPC + MPO
Polarity	Method A
Total Fibers, quantity	20
Total Ports, quantity, front	21
Total Ports, quantity, rear	0
Dimensions	
Height	129.03 mm   5.08 in
Width	28.96 mm   1.14 in
Depth	76.2 mm   3 in
Optical Specifications	
Fiber Mode	Multimode
Fiber Type	OM4
Insertion Loss, maximum	0.66 dB
FunctionalityAdapter ColorInterface, frontPolarityTotal Fibers, quantityTotal Ports, quantity, frontTotal Ports, quantity, rearDimensionsHeightWidthDepthOptical SpecificationsFiber ModeFiber Type	Aqua LC/UPC + MPO Method A 20 21 0 129.03 mm   5.08 in 28.96 mm   1.14 in 76.2 mm   3 in Multimode 0M4

### **Environmental Specifications**

Safety Standard UL

# Packaging and Weights

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 25, 2023



### DM2-020-LS-MP024-LC 760248413

#### Packaging quantity

### Regulatory Compliance/Certifications

#### Agency

#### Classification

CHINA-ROHS

# ROHS

**UK-ROHS** 



Above maximum concentration value Compliant/Exempted

Compliant/Exempted

1



Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: November 25, 2023

