



Fiber OSP cable, HDPE, 8-fiber, Singlemode, loose tube, gel-filled, Singlemode G.652.D and G.657.A1, Meters jacket marking, Black jacket color, 1000 m. Provides Rodent Resistance

Product Classification

Regional Availability	Australia/New Zealand EMEA
Portfolio	CommScope®
Product Type	Fiber OSP cable
Product Series	O-CA

General Specifications

Armor Type	Corrugated steel
Cable Type	Loose tube
Subunit Type	Gel-filled
Jacket Color	Black
Jacket Marking	Meters
Jacket Marking Method	Inkjet
Jacket Marking Text	COMMScope GB SYSTEM F.O. CABLE 810009834/DB CSA GEL LOOSE TUBE 8X9 /125 OS2 HDPE (Serial NUMBER) (METRE MARK)
Fibers per Subunit, quantity	8
Total Fiber Count	8

Dimensions

Cable Length	1000 m 3,280.84 ft
Diameter Over Jacket	10 mm 0.394 in

Material Specifications

Jacket Material	High density polyethylene (HDPE)
-----------------	----------------------------------

Mechanical Specifications

Minimum Bend Radius, loaded	150 mm 5.906 in
Minimum Bend Radius, unloaded	100 mm 3.937 in

810009834/DB | O-008-CA-8W-M08BK/GY/HD

Tensile Load, long term, maximum	1250 N 281.011 lbf
Flex	25 cycles

Optical Specifications

Fiber Type	OS2
------------	-----

Optical Specifications, Wavelength Specific

Attenuation, maximum	0.25 dB/km @ 1,300 nm 0.35 dB/km @ 1,550 nm 0.45 dB/km @ 1,310 nm
Standards Compliance	TIA-492CAAB (OS2)

Environmental Specifications

Installation temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Operating Temperature	-20 °C to +70 °C (-4 °F to +158 °F)
Storage Temperature	-20 °C to +70 °C (-4 °F to +158 °F)

Packaging and Weights

Cable weight	104 kg/km 69.885 lb/kft
--------------	---------------------------

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Included Products

CS-8W-250-EMEA – LightScope® ZWP Singlemode Fiber
8W-250um

* Footnotes

Operating Temperature Specification applicable to non-terminated bulk fiber cable