

AVA6P-50-42



AVA6-50, HELIAX® Andrew Virtual Air™ Premium Coaxial Cable, corrugated copper, 1-1/4 in, black PE jacket

Product Classification

Product Type	Coaxial wireless cable
Product Brand	HELIAX®
Product Series	AVA6-50
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa Not available in the United States or Canada

General Specifications

Product Number	520099502/00
Flexibility	Standard
Jacket Color	Black
Performance Note	Attenuation values typical, guaranteed within 5%

Dimensions

Diameter Over Dielectric	34.036 mm 1.34 in
Diameter Over Jacket	39.624 mm 1.56 in
Inner Conductor OD	14.021 mm 0.552 in
Outer Conductor OD	36.068 mm 1.42 in
Nominal Size	1-1/4 in

Electrical Specifications

Cable Impedance	50 ohm ±1 ohm
Capacitance	72 pF/m 21.946 pF/ft
dc Resistance, Inner Conductor	1.74 ohms/km 0.53 ohms/kft
dc Resistance, Outer Conductor	0.75 ohms/km 0.229 ohms/kft
dc Test Voltage	8500 V
Inductance	0.187 µH/m 0.057 µH/ft
Insulation Resistance	100000 MOhms-km

AVA6P-50-42

Jacket Spark Test Voltage (rms)	10000 V
Operating Frequency Band	1 – 4000 MHz
Peak Power	180 kW
Velocity	92 %

VSWR/Return Loss

Frequency Band	VSWR	Return Loss (dB)
450–680 MHz	1.101	26.36
680–800 MHz	1.101	26.36
806–960 MHz	1.101	26.36
1700–2200 MHz	1.101	26.36

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)	Average Power (kW)
1.0	0.079	0.024	82.63
1.5	0.097	0.03	67.41
2.0	0.113	0.034	58.33
10.0	0.253	0.077	25.89
20.0	0.36	0.11	18.21
30.0	0.443	0.135	14.8
50.0	0.576	0.176	11.39
85.0	0.758	0.231	8.66
88.0	0.772	0.235	8.51
100.0	0.825	0.251	7.96
108.0	0.858	0.262	7.65
150.0	1.019	0.311	6.44
174.0	1.102	0.336	5.96
200.0	1.186	0.361	5.53
204.0	1.198	0.365	5.48
300.0	1.471	0.448	4.46
400.0	1.717	0.523	3.82
450.0	1.829	0.558	3.59
460.0	1.851	0.564	3.54
500.0	1.937	0.59	3.39
512.0	1.962	0.598	3.34

AVA6P-50-42

600.0	2.14	0.652	3.07
700.0	2.329	0.71	2.82
800.0	2.507	0.764	2.62
824.0	2.548	0.777	2.58
894.0	2.666	0.813	2.46
960.0	2.774	0.846	2.37
1000.0	2.838	0.865	2.31
1218.0	3.171	0.967	2.07
1250.0	3.218	0.981	2.04
1500.0	3.569	1.088	1.84
1700.0	3.835	1.169	1.71
1794.0	3.955	1.206	1.66
1800.0	3.963	1.208	1.66
2000.0	4.212	1.284	1.56
2100.0	4.333	1.321	1.51
2200.0	4.452	1.357	1.47
2300.0	4.569	1.393	1.44
2500.0	4.798	1.462	1.37
2700.0	5.021	1.53	1.31
3000.0	5.345	1.629	1.23
3400.0	5.76	1.755	1.14
3600.0	5.961	1.817	1.1
3700.0	6.06	1.847	1.08
3800.0	6.16	1.877	1.07
4000.0	6.36	1.94	1.03

Material Specifications

Dielectric Material	Foam PE
Jacket Material	PE
Inner Conductor Material	Corrugated copper tube
Outer Conductor Material	Corrugated copper

Mechanical Specifications

Minimum Bend Radius, multiple Bends	203.2 mm 8 in
Minimum Bend Radius, single Bend	152.4 mm 6 in

AVA6P-50-42

Number of Bends, minimum	15
Number of Bends, typical	40
Tensile Strength	154 kg 339.511 lb
Bending Moment	29.8 N-m 263.752 in lb
Flat Plate Crush Strength	1.3 kg/mm 72.797 lb/in

Environmental Specifications

Installation temperature	-40 °C to +60 °C (-40 °F to +140 °F)
Operating Temperature	-55 °C to +85 °C (-67 °F to +185 °F)
Storage Temperature	-70 °C to +85 °C (-94 °F to +185 °F)
Attenuation, Ambient Temperature	68 °F 20 °C
Average Power, Ambient Temperature	104 °F 40 °C
Average Power, Inner Conductor Temperature	212 °F 100 °C

Packaging and Weights

Cable weight	0.68 kg/m 0.457 lb/ft
---------------------	-------------------------

Regulatory Compliance/Certifications

Agency	Classification
CENELEC	EN 50575 compliant, Declaration of Performance (DoP) available
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

