


760117960 | MFC-SCF-09-6X QWIK II™ SC



Qwik II® Field Installable SC Connector, OM1, Beige, for 250/900um, single pack

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber connector
Product Brand	OptiSPEED® Qwik II®
Product Series	Qwik II

General Specifications

Body Style	BTW
Color, boot	Black
Color, housing	Beige
Ferrule Geometry	Factory polished
Interface	SC/UPC
Interface Feature	Field Installable Mechanical splice

Dimensions

Length	50.2 mm 1.976 in
Compatible Cable Diameter	0.25 mm 0.01 in 0.9 mm 0.035 in

Material Specifications

Ferrule Material	Zirconia
-------------------------	----------

Mechanical Specifications

Cable Retention Strength, maximum	1.00 lb @ 0 °
--	---------------

Optical Specifications

Fiber Mode	Multimode
Fiber Type	OM1

760117960 | MFC-SCF-09-6X QWIK II™ SC

Insertion Loss Change, mating	0.3 dB
Optical Components Standard	ANSI/TIA-568. 3-D
Insertion Loss Change, temperature	0.3 dB
Insertion Loss, maximum	0.5 dB
Insertion Loss, typical	0.1 dB
Return Loss, minimum	20 dB

Environmental Specifications

Operating Temperature -40 °C to +75 °C (-40 °F to +167 °F)

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



* Footnotes

Insertion Loss Change, mating TIA-568: Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)