## **Base Product**



## SL-Series Modular Jack, RJ45, Cat6 Shielded

## **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America

Portfolio NETCONNECT®

Product Type Modular jack

Product Series SLX Series

General Specifications

ANSI/TIA Category 6

Cable Type Shielded

Conductor Type Solid | Stranded

**Mounting** SL Series faceplates and panels

Outlet Type Standard

**Termination Tool** SL Termination tool

Termination Type IDC

**Transmission Standards**ANSI/TIA-568-C.2 | ISO/IEC 11801 Class E

**Wiring** T568A | T568B

Dimensions

**Panel Cutout, recommended** 14.78 x 20.07 mm (0.58 x 0.79 in)

 Height
 16.13 mm | 0.635 in

 Width
 14.44 mm | 0.569 in

 Depth
 36.8 mm | 1.449 in

Compatible Cable Diameter, maximum8.5 mm0.335 inCompatible Insulated Conductor Diameter, maximum1.6 mm0.063 in

 Contact Plating Thickness
 1.27 μm

Compatible Conductor Gauge, solid 26–22 AWG



## 2153448

**Compatible Conductor Gauge, stranded** 26–24 AWG

**Electrical Specifications** 

Remote Powering Fully supports the safe delivery of power over LAN cabling described

by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002

**PoE Durability** Supports IEEE 802.3bt Type 4 (90 W) applications greater than 3000

plug to jack mating cycles

Material Specifications

Contact Base Material Beryllium copper

Contact Plating Material Gold

Material Type Polycarbonate | Zamak

Mechanical Specifications

Plug to Jack Mating Cycles Complies to IEC 60603-7 series

**Environmental Specifications** 

Operating Temperature  $-10 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Flammability Rating UL 94 V-0

Packaging and Weights

Packaging Type Bag | Box