
## 810009685/DB | 0-072-LN-8W-M12NS/20G/HTS



Fiber OSP cable, LightSCOPE® Mini Single Jacket All-Dielectric, High Tensile Strength, Gel-Filled, Outdoor Stranded Loose Tube, 72 fiber, Singlemode G.652.D and G.657.Al, Meters jacket marking, Black jacket color. Provides Rodent Resistance

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA

Portfolio CommScope®
Product Type Fiber OSP cable

**Product Series** O-LN

General Specifications

Cable Type Stranded loose tube

Construction Type Non-armored

Subunit Type Gel-filled

Filler, quantity 0

Jacket ColorBlackJacket MarkingMetersJacket Marking MethodInkjet

Jacket Marking Text COMMSCOPE GB OPTICAL CABLE 810009685/DB OS2 SM 72 MDPE [SERIAL NUMBER]

[METRE MARK]

Subunit, quantity 6
Fibers per Subunit, quantity 12
Total Fiber Count 72


**Dimensions** 

**Buffer Tube/Subunit Diameter** 2 mm | 0.079 in **Diameter Over Jacket** 11.6 mm | 0.457 in

## Representative Image



# 810009685/DB | 0-072-LN-8W-M12NS/20G/HTS



### Material Specifications

Jacket Material PE

## Mechanical Specifications

Minimum Bend Radius, loaded174 mm | 6.85 inMinimum Bend Radius, unloaded116 mm | 4.567 inTensile Load, long term, maximum1350 N | 303.492 lbfTensile Load, short term, maximum4500 N | 1,011.641 lbfCompression22 N/mm | 125.623 lb/inCompression Test MethodFOTP-41 | IEC 60794-1 E3

Flex 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

**Strain Test Method** FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

**Twist Test Method** FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 1345 m | 4,412.73 ft

Optical Specifications

**Fiber Type** G.652.D and G.657.A1 | OS2

## **Environmental Specifications**



## 810009685/DB | 0-072-LN-8W-M12NS/20G/HTS

Installation temperature  $-10 \,^{\circ}\text{C}$  to  $+50 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +122  $^{\circ}\text{F}$ )

Operating Temperature  $-30 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (-22  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-87-640 | EN 187105 | IEC 60794-1-2

Jacket UV Resistance UV stabilized

Water Penetration 24 h

**Water Penetration Test Method** FOTP-82 | IEC 60794-1 F5

### **Environmental Test Specifications**

**Cable Freeze** -2 °C | 28.4 °F

**Cable Freeze Test Method** FOTP-98 | IEC 60794-1 F15

**Drip** 70 °C | 158 °F

**Drip Test Method** FOTP-81 | IEC 60794-1 E14

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend**  $-15 \,^{\circ}\text{C}$  to  $+40 \,^{\circ}\text{C}$  (+5  $^{\circ}\text{F}$  to  $+104 \,^{\circ}\text{F}$ )

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle** -30 °C to +60 °C (-22 °F to +140 °F)

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 111 kg/km | 74.589 lb/kft

#### Included Products

CS-8W-250-EMEA – LightScope® ZWP Singlemode Fiber 8W-250um

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable



# CS-8W-250-EMEA | 8W-250um

### LightScope® ZWP Singlemode Fiber



#### **Product Classification**

 Portfolio
 CommScope®

 Product Type
 Optical fiber

General Specifications

**Cladding Diameter** 125 µm **Cladding Diameter Tolerance** ±0.7 µm Cladding Non-Circularity, maximum 0.7 % **Coating Diameter (Colored)** 249 µm **Coating Diameter (Uncolored)** 242 µm **Coating Diameter Tolerance (Colored)** ±13 μm **Coating Diameter Tolerance (Uncolored)** ±7 μm Coating/Cladding Concentricity Error, maximum 12 µm Core/Clad Offset, maximum 0.5 µm

Proof Tensile Stress 100,000 psi (0.69 GPa)

Dimensions

Fiber Curl, minimum 4 m | 13.123 ft

Mechanical Specifications

 Macrobending, 20 mm Ø mandrel, 1 turn
 0.75 dB @ 1,550 nm
 | 1.50 dB @ 1,625 nm

 Macrobending, 30 mm Ø mandrel, 10 turns
 0.25 dB @ 1,550 nm
 | 1.00 dB @ 1,625 nm

 Macrobending, 60 mm Ø mandrel, 100 turns
 0.05 dB @ 1,550 nm
 | 0.05 dB @ 1,625 nm

Coating Strip Force, maximum8.9 N | 2.001 lbfCoating Strip Force, minimum1.3 N | 0.292 lbf

Dynamic Fatigue Parameter, minimum 20

Optical Specifications



## CS-8W-250-EMEA | 8W-250um

Cabled Cutoff Wavelength, maximum1250 nmPoint Defects, maximum0.05 dB

**Zero Dispersion Slope, maximum** 0.092 ps/[km-nm-nm]

Zero Dispersion Wavelength, maximum1324 nmZero Dispersion Wavelength, minimum1300 nm

Optical Specifications, Wavelength Specific

**Attenuation, maximum** 0.20 dB/km @ 1,550 nm | 0.23 dB/km @ 1,625

nm | 0.344 dB/km @ 1310 nm | 0.344 dB/km @ 1380

- 1385 nm

**Dispersion, maximum** 18 ps(nm-km) at 1550 nm | 22 ps(nm-km) at 1625

nm | 3.5 ps(nm-km) from 1285 nm to 1330 nm at 1310

nm

**Index of Refraction** 1.467 @ 1,310 nm | 1.467 @ 1,385 nm | 1.468 @ 1,550

nm

 $\textbf{Mode Field Diameter} \hspace{15mm} 10.4~\mu\text{m} \ \textcircled{@} \ 1,550~\text{nm} \hspace{0.25mm} | \hspace{0.25mm} 9.2~\mu\text{m} \ \textcircled{@} \ 1,310~\text{nm}$ 

**Mode Field Diameter Tolerance**  $\pm 0.4 \,\mu\text{m}$  @ 1310 nm |  $\pm 0.5 \,\mu\text{m}$  @ 1550 nm

**Polarization Mode Dispersion Link Design Value, maximum** 0.05 ps/sqrt(km)

Standards Compliance ITU-T G.652.D | ITU-T G.657.A1

### **Environmental Specifications**

Heat Aging, maximum 0.05 dB/km @ 85 °C

Temperature Dependence, maximum0.05 dB/kmTemperature Humidity Cycling, maximum0.05 dB/km

Water Immersion, maximum 0.05 dB/km @ 23 °C

#### \* Footnotes

**Temperature Dependence, maximum** Temperature dependence is conducted at -60 °C to +85 °C (-76 °F to +185 °F)

**Temperature Humidity Cycling, maximum** Temperature humidity cycling is conducted at -10 °C to +85 °C (+14 °F to +185 °F)

up to 95% relative humidity

