# 810009685/DB | 0-072-LN-8W-M12NS/20G/HTS



Fiber OSP cable, LightSCOPE® Mini Single Jacket All-Dielectric, High Tensile Strength, Gel-Filled, Outdoor Stranded Loose Tube, 72 fiber, Singlemode G.652.D and G.657.Al, Meters jacket marking, Black jacket color. Provides Rodent Resistance

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA

Portfolio CommScope®
Product Type Fiber OSP cable

**Product Series** O-LN

General Specifications

Cable Type Stranded loose tube

Construction Type Non-armored

**Subunit Type** Gel-filled

Filler, quantity 0

Jacket Color Black

Jacket Marking Method Inkjet

Jacket Marking Text COMMSCOPE GB OPTICAL CABLE 810009685/DB OS2 SM 72 MDPE [SERIAL NUMBER]

[METRE MARK]

Subunit, quantity 6
Fibers per Subunit, quantity 12
Total Fiber Count 72


**Dimensions** 

**Buffer Tube/Subunit Diameter** 2 mm | 0.079 in **Diameter Over Jacket** 11.6 mm | 0.457 in

## Representative Image



# 810009685/DB | 0-072-LN-8W-M12NS/20G/HTS



### Material Specifications

Jacket Material PE

### Mechanical Specifications

Minimum Bend Radius, loaded174 mm | 6.85 inMinimum Bend Radius, unloaded116 mm | 4.567 inTensile Load, long term, maximum1350 N | 303.492 lbfTensile Load, short term, maximum4500 N | 1,011.641 lbfCompression22 N/mm | 125.623 lb/inCompression Test MethodFOTP-41 | IEC 60794-1 E3

**Flex** 25 cycles

Flex Test Method FOTP-104 | IEC 60794-1 E6

**Impact** 2.94 N-m | 26.021 in lb

Impact Test Method FOTP-25 | IEC 60794-1 E4

**Strain** See long and short term tensile loads

Strain Test Method FOTP-33 | IEC 60794-1 E1

Twist 10 cycles

**Twist Test Method** FOTP-85 | IEC 60794-1 E7

**Vertical Rise, maximum** 1345 m | 4,412.73 ft

**Optical Specifications** 

**Fiber Type** G.652.D and G.657.A1 | OS2

### **Environmental Specifications**



## 810009685/DB | 0-072-LN-8W-M12NS/20G/HTS

Installation temperature  $-10 \,^{\circ}\text{C}$  to  $+50 \,^{\circ}\text{C}$  (+14  $^{\circ}\text{F}$  to +122  $^{\circ}\text{F}$ )

Operating Temperature  $-30 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (-22  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Storage Temperature  $-40 \,^{\circ}\text{C}$  to  $+70 \,^{\circ}\text{C}$  (-40  $^{\circ}\text{F}$  to +158  $^{\circ}\text{F}$ )

Cable Qualification Standards ANSI/ICEA S-87-640 | EN 187105 | IEC 60794-1-2

Jacket UV Resistance UV stabilized

Water Penetration 24 h

**Water Penetration Test Method** FOTP-82 | IEC 60794-1 F5

#### **Environmental Test Specifications**

**Cable Freeze** -2 °C | 28.4 °F

**Cable Freeze Test Method** FOTP-98 | IEC 60794-1 F15

**Drip** 70 °C | 158 °F

**Drip Test Method** FOTP-81 | IEC 60794-1 E14

**Heat Age** 0 °C to +85 °C (+32 °F to +185 °F)

**Heat Age Test Method** IEC 60794-1 F9

**Low High Bend**  $-15 \,^{\circ}\text{C}$  to  $+40 \,^{\circ}\text{C}$  (+5  $^{\circ}\text{F}$  to  $+104 \,^{\circ}\text{F}$ )

**Low High Bend Test Method** FOTP-37 | IEC 60794-1 E11

**Temperature Cycle**  $-30 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (-22  $^{\circ}\text{F}$  to  $+140 \,^{\circ}\text{F}$ )

**Temperature Cycle Test Method** FOTP-3 | IEC 60794-1 F1

Packaging and Weights

Cable weight 111 kg/km | 74.589 lb/kft

#### Included Products

CS-8W-250-EMEA – LightScope® ZWP Singlemode Fiber 8W-250um

#### \* Footnotes

**Operating Temperature** Specification applicable to non-terminated bulk fiber cable

