


CBC6AE7LT-DS-43 | E14F05P67



Twin Diplexer, 600AE/700LABC, DC Sense, 4.3-10

- Automatic dc switching with dc sense
- Convertible mounting brackets
- Stackable in multiples with included hardware
- New 4.3-10 connectors for improved PIM performance and size reduction

OBSOLETE

This product was discontinued on: **March 30, 2024**

Replaced By:

E14F06P51

Quad Diplexer 617-698/703-960 MHz, 4.3-10 connectors

Product Classification

Product Type Diplexer

General Specifications

Color Gray

Common Port Label COMM

Modularity 2-Twin

Mounting Pole | Wall

Mounting Pipe Hardware Band clamps (2)

RF Connector Interface 4.3-10 Female

RF Connector Interface Body Style Long neck

Dimensions

Height 177 mm | 6.969 in


Width 181 mm | 7.126 in

Depth 131 mm | 5.157 in

Ground Screw Diameter 6 mm | 0.236 in

CBC6AE7LT-DS-43 | E14F05P67

Outline Drawing



Electrical Specifications

Impedance	50 ohm
License Band, Band Pass	CEL 850 USA 600 USA 700 USA 750

Electrical Specifications, Common Port

Composite Power, PEP	250 W
-----------------------------	-------

Electrical Specifications, dc Power/Alarm

dc/AISG Pass-through Method	Auto sensing
dc/AISG Pass-through Path	See logic table
Lightning Surge Current	10 kA

CBC6AE7LT-DS-43 | E14F05P67

Lightning Surge Current Waveform

8/20 waveform


Electrical Specifications

Sub-module	1 2	1 2
Branch	1	2
License Band	USA 600, Band Pass	USA 700, Band Pass

Electrical Specifications, Band Pass

Frequency Range, MHz	617.25–687.75	699.25–745.75
Insertion Loss, maximum, dB	0.45	0.45
Insertion Loss, typical, dB	0.2	0.2
Total Group Delay, maximum, ns	75	70
Return Loss, typical, dB	22	22
Isolation, typical, dB	53	48
Input Power, RMS, maximum, W	200	200
Input Power, PEP, maximum, W	2000	2000
3rd Order PIM, typical, dBc	-161	-161
3rd Order PIM Test Method	2 x 20 W CW tones	2 x 20 W CW tones

Block Diagram



Logic Table

Combining Mode Operation (Ground Based)			
RF Ports Input Voltage			
617.25 to 687.75 MHz	699.25 to 745.75 MHz	COMMON	DC/AISG Path Selection
$7 \leq V \leq 30$	<7	<7	617.25 to 687.75 MHz to COMMON "ON"
<7	$7 \leq V \leq 30$	<7	699.25 to 745.75 MHz to COMMON "ON"
$7 \leq V \leq 30$	$7 \leq V \leq 30$	<7	617.25 to 687.75 MHz to COMMON "ON"
Splitting Mode Operation (Tower Top)			
RF Ports Impedance DC (Load sensing)			
617.25 to 687.75 MHz	699.25 to 745.75 MHz	COMMON	DC/AISG Path Selection
open/load	short	$7 \leq V \leq 30$	COMMON to 617.25-687.75 "ON"
short	open/load	$7 \leq V \leq 30$	COMMON to 699.25-745.75 "ON"
open/load	open/load	$7 \leq V \leq 30$	ALL ports ON
short	short	$7 \leq V \leq 30$	ALL ports OFF

Environmental Specifications

Operating Temperature	-40 °C to +65 °C (-40 °F to +149 °F)
Relative Humidity	5%–100%
Corrosion Test Method	IEC 60068-2-11, 30 days
Ingress Protection Test Method	IEC 60529:2001, IP67

Packaging and Weights

Included	Mounting hardware
Mounting Hardware Weight	0.5 kg 1.102 lb
Weight, without mounting hardware	5.3 kg 11.684 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system