## CT-10-TUW-NI6



Product Classification

10 dB, Tapper, 340 – 6000 MHz

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America
Product Type	Tapper
General Specifications	
Device Type	Tapper
Application	Indoor/Outdoor
Color	White
Inner Contact Plating	Silver
Interface	N Female
Outer Contact Plating	Trimetal
Dimensions	
Height	25 mm   0.984 in
Width	43 mm   1.693 in
Length	141 mm   5.551 in
Electrical Specifications	
3rd Order IMD	-163 dBc
3rd Order IMD Test Method	Two +43 dBm carriers
Insertion Loss at Frequency Band	0.7 dB @ 1695–2700 MHz   0.7 dB @ 340–960 MHz   0.75 dB @ 3500–4500 MHz   0.75 dB @ 4900–6000 MHz
Return Loss at Frequency Band	19.1 dB @ 3500-4500 MHz   19.1 dB @ 4900-6000 MHz   20.8 dB @ 1695-2700 MHz   20.8 dB @ 340-960 MHz
Average Power, maximum	200 W
Coupling	10 dB
Coupling Tolerance	+0.1/-1.1dB @ 4900-6000 MHz   +0/-0.8dB @ 380-520 MHz   +0/-1.3dB @ 340-380 MHz   +0/-1.5dB @ 3500-4500 MHz   ±0.45dB @ 698-960 MHz   ±0.7dB @ 1695- 2700 MHz

Page 1 of 2



# CT-10-TUW-NI6

Impedance	50 ohm
Operating Frequency Band	1695 – 2700 MHz   340 – 960 MHz   3500 – 4500 MHz   4900 – 6000 MHz
Peak Power, maximum	3 kW
Reflected Power, maximum	200 W
Mechanical Specifications	

Coupling Nut Proof Torque 4.5 N-m | 39.828 in lb

### **Environmental Specifications**

Operating Temperature	-35 °C to +85 °C (-31 °F to +185 °F)
Relative Humidity	Up to 100%
Corrosion Test Method	IEC 60068-2-11, 30 days
Ingress Protection Test Method	IEC 60529:2001, IP67

### Packaging and Weights

Height, packed	40 mm   1.575 in
Width, packed	90 mm   3.543 in
Length, packed	180 mm   7.087 in
Weight, gross	0.3 kg   0.661 lb
Weight, net	0.25 kg   0.551 lb

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted





Page 2 of 2

©2025 ANDREW, an Amphenol company. All rights reserved. Amphenol and ANDREW are registered trademarks of Amphenol and/or its affiliates in the U.S. and other countries. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 12, 2025