

H-4X4-CPUSE-NAI6

Low PIM 4x4 High Power Hybrid Matrix, 555–2 700 MHz



Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Product Type	Hybrid matrix

General Specifications

Device Type	Hybrid
Application	Indoor/Outdoor
Color	Silver
Inner Contact Plating	Silver
Interface	N Female
Outer Contact Plating	Trimetal

Dimensions

Height	31 mm 1.22 in
Width	181 mm 7.126 in
Length	181 mm 7.126 in

Electrical Specifications

3rd Order IMD	-160 dBc
3rd Order IMD Test Method	Two +43 dBm carriers
Insertion Loss at Frequency Band	0.3 dB @ 555–2700 MHz
Return Loss, minimum	20.8 dB
Average Power, maximum	100 W
Coupling	6.2 dB
Coupling Tolerance	±1.0dB @ 698–2700 MHz ±2.5dB @ 555–698 MHz
Impedance	50 ohm

H-4X4-CPUSE-NAI6

Isolation at Frequency Band	25 dB @ 555–2700 MHz
Operating Frequency Band	555 – 2700 MHz
Peak Power, maximum	1 kW
Reflected Power, maximum	100 W
VSWR	1.2

Mechanical Specifications

Coupling Nut Proof Torque	4.5 N-m 39.828 in lb
----------------------------------	------------------------

Environmental Specifications

Operating Temperature	-35 °C to +85 °C (-31 °F to +185 °F)
Relative Humidity	Up to 100%
Ingress Protection Test Method	IEC 60529:2001, IP65

Packaging and Weights

Height, packed	45 mm 1.772 in
Width, packed	210 mm 8.268 in
Length, packed	210 mm 8.268 in
Weight, gross	2 kg 4.409 lb
Weight, net	1.5 kg 3.307 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

