



GigaSPEED X10D® VisiPatch® 360 to VisiPatch® 360 4-pair Solid Low Smoke Zero Halogen Patch Cord

Product Classification

Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America
Portfolio	SYSTIMAX®
Product Type	Twisted pair patch cord
Product Brand	GigaSPEED X10D®   VisiPatch 360®
Product Series	CPC
Ordering Note	Cords < 2 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords   Cords > 2 m are authorized for use in channels and are an effective standalone method used to connect active devices

General Specifications

ANSI/TIA Category	6A
Cable Type	U/UTP (unshielded)
Conductor Type	Solid
Interface, Connector A	VisiPatch® 360
Interface Feature, connector A	Standard
Interface, Connector B	VisiPatch® 360
Interface Feature, connector B	Standard
Jacket Color	Black   Blue   Dark gray   Light blue   Lilac   Orange   Red   Slate   Spring green   White   Yellow
Pairs, quantity	4
Transmission Standards	IEEE 802.3bt Type 4
Wiring	VisiPatch® 360

Dimensions

Cable Assembly Length Range (m)	1 – 30
---------------------------------	--------

# CPCFFZ2

Cable Assembly Length Range (ft)	3 – 100
Diameter Over Jacket	7.24 mm   0.285 in
Compatible Conductor Gauge, solid	24 AWG   24 AWG

## Wiring Diagram

	Connector A	Connector B
Position 1	Blue	Blue
Position 2	Lt. Blue	Lt. Blue
Position 3	Orange	Orange
Position 4	White/Orange	White/Orange
Position 5	Green	Green
Position 6	Lt. Green	Lt. Green
Position 7	Brown	Brown
Position 8	Lt. Brown	Lt. Brown

## Electrical Specifications

dc Resistance, maximum	0.3 ohm
------------------------	---------

## Ordering Tree

CPC-

9

10

11

12

0

1

F

0

5

0

Outlet Color	
9	0 Not applicable
	1 Black
	2 Blue
	3 Gray
	4 Green
	5 Ivory
	6 Orange
	7 Red
	8 White
	9 Yellow
	B Lilac

Jacket Color	
10	1 Black
	2 Light blue
	3 Dark gray
	4 Spring green
	5 Ivory
	6 Orange
	7 Red
	8 White
	9 Yellow
	B Lilac
	C Gray
	K Pink
	L Violet
	M Green
	Z Blue

UOM		
11	F	Foot
	M	Meter
	N	Inch
	C	Centimeter

Length	
12	xxx

- Notes
- Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices
  - Cords < 1m are also valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords

Material Specifications

Contact Plating Material	Precious metals
Material Type	Copper alloy   Polycarbonate

Mechanical Specifications

Plug Insertion Life, minimum	200 times
Plug Retention Force, minimum	44 N   9.892 lbf

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Acid Gas Test Method	IEC 60754-2
Environmental Space	Low Smoke Zero Halogen (LSZH)
Flame Test Method	IEC 60332-3-22
Flammability Rating	UL 94 V-0
Safety Standard	ETL   cETL

Packaging and Weights

Packaging quantity	1
--------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

